

UM-TM (3,5X10) - Marker for terminal blocks



0830952

<https://www.phoenixcontact.com/gb/products/0830952>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker for terminal blocks, Strip, white, unmarked, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: latching, Number of individual labels: 34, text field height: 10 mm, text field width: 3.5 mm



Your advantages

- The markers, which are supplied in uniform strips, can be printed onto quickly and easily using the BLUEMARK printing systems
- The UM-TM ... UM labeling range includes terminal markers for Phoenix Contact terminal blocks with tall marker groove
- The multi-section marking strips are easy to fit and can be easily separated if required
- The markers support multi-line labeling

Commercial data

Item number	0830952
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BGE21C
Product key	BGE21C
GTIN	4046356910880
Weight per piece (including packing)	2.26 g
Weight per piece (excluding packing)	2.041 g
Customs tariff number	39269097
Country of origin	PL

UM-TM (3,5X10) - Marker for terminal blocks



0830952

<https://www.phoenixcontact.com/gb/products/0830952>

Technical data

Product properties

Product type	Klemmenmarker
Area of application	Phoenix Contact

Marking

Number of individual labels	34
Number of individual labels per row	17
Number of marker strips	2
Identification technology	UV LED technology

Dimensions

Width	2.95 mm
Height	10.49 mm
Depth	4.20 mm

Material specifications

RoHS compliant	yes
Color	white (RAL 9010)
Flammability rating according to UL 94	V2
Base element material	PC
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed

UM-TM (3,5X10) - Marker for terminal blocks



0830952

<https://www.phoenixcontact.com/gb/products/0830952>

Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	latching
---------------	----------

UM-TM (3,5X10) - Marker for terminal blocks



0830952

<https://www.phoenixcontact.com/gb/products/0830952>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UM-TM (3,5X10) - Marker for terminal blocks



0830952

<https://www.phoenixcontact.com/gb/products/0830952>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.01 kg CO2e
---------	--------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk