# Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



# Basic HMI Gateway Box STM6 for Faceless HMI application

HMISTM6BOX

EAN Code: 3606481856432

### Main

Range of product	Harmony STM6	
Product or component type	Modular HMI box	
Software package	EcoStruxure Operator Terminal Expert Web viewer	
Operating system	Linux	
Processor name	ARM Cortex-A8	
Processor frequency	800 MHz	
Data storage equipment	1 GB Flash disk NAND	
Memory description	512 KB backup memory 512 MB internal 1 GB flash	

# Complementary

[Us] rated supply voltage	24 V DCpower supply	
Local signalling	LED multi-colour for status	
Port Ethernet	10BASE-T/100BASE-T	
Integrated connection type	2 Ethernet TCP/IP - RJ45 COM1 serial link - SUB-D 9 - RS232C/RS422/RS485 (rate: 2400115200 bps) USB 2.0 port - micro B USB display port - RJ45 1 USB 2.0 port - USB type A	
Type of cooling	Natural convection	
Realtime clock	Built-in	
Height	101 mm	
Width	150.5 mm	
Depth	63.3 mm	
Net weight	0.456 kg	

### **Environment**

Standards	CSA C22.2 No 142	
	ANSI/ISA 12-12-01	
	UL 508	
	CSA C22.2 No 213	
	IEC 61132-2	

Product certifications	CE		
	UKCA		
	cULus		
	RCM		
	KC		
	cULus Class 1 Division 2		
	DNV		
	ABS		
	RINA		
	BV		
Pollution degree	2 conforming to IEC 61131-2 ed.3		
Ambient air temperature for operation	060 °C		
Ambient air temperature for storage	-2060 °C		
Relative humidity	1090 % non-condensing		
Operating altitude	2000		
Shock resistance	147 m/s² conforming to IEC 61131-2		
Vibration resistance	3.5 mm constant amplitude (f = $59$ Hz) conforming to IEC 61131-2 9.8 m/s <sup>2</sup> (f = $9150$ Hz) conforming to IEC 61131-2		
Electromagnetic compatibility	Electrostatic discharge immunity test conforming to IEC 61000-4-2 level 3		

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	17.6 cm
Package 1 Length	26.5 cm
Package 1 Weight	675.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	6
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.895 kg

# **Logistical informations**

Country of origin

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

### Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	279
Environmental Disclosure	Product Environmental Profile

### **Use Better**

<b>⊗</b> Materials and Substances	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	715da6e9-302b-4bd3-a8b4-7f8cdd474a0e
REACh Regulation	REACh Declaration


### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No

### **Dimensions Drawings**


### **Dimensions**

### **External dimensions**



(1): Front(2): Right(3): Bottom

### Dimension with installation adapter




(1) : Front (2) : Right

### Dimension with separation cable

### **Product datasheet**

### **HMISTM6BOX**



(1) : Front (2) : Right

(3): To assemble this product, 20 mm (0.78 in) or more space required to bend the rubber portion at the end of the cable.