



SAFETY DATA SHEET
FLAWFINDER DYE PENETRANT SPRAY

Page: 1

Compilation date: 01/03/2013

Revision No: 12

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: FLAWFINDER DYE PENETRANT SPRAY

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Dye penetrant.

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CHIP: F+: R12; -: R66

Most important adverse effects: Extremely flammable. Repeated exposure may cause skin dryness or cracking.

2.2. Label elements

Label elements under CHIP:

Hazard symbols: Extremely flammable.



Risk phrases: R12: Extremely flammable.

R66: Repeated exposure may cause skin dryness or cracking.

Safety phrases: S16: Keep away from sources of ignition - No smoking.

S24: Avoid contact with skin.

S51: Use only in well-ventilated areas.

Precautionary phrases: Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

[cont...]

SAFETY DATA SHEET
FLAWFINDER DYE PENETRANT SPRAY

Page: 2

2.3. Other hazards

PBT: This substance is not identified as a PBT substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

CARBON DIOXIDE AEROSOL PROPELLANT

EINECS	CAS	CHIP Classification	CLP Classification	Percent
204-696-9	124-38-9	-:	-	1-10%

ISOPARAFFINIC HYDROCARBON

265-149-8	64742-47-8	Xn: R65; -: R66	-	30-50%
-----------	------------	-----------------	---	--------

WHITE MINERAL OIL

232-455-8	8042-47-5	-	-	50-70%
-----------	-----------	---	---	--------

PETROLEUM DISTILLATE (SEVERE) HYDROTREATED

-	64742-53-6	Xn: R20	-	1-10%
---	------------	---------	---	-------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. Consult a doctor.

Inhalation: Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Use water spray to cool containers. Alcohol resistant foam. Dry chemical powder.
Carbon dioxide. Do not use water.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

[cont...]

SAFETY DATA SHEET
FLAWFINDER DYE PENETRANT SPRAY

Page: 3

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Eliminate all sources of ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Do not handle in a confined space.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep away from direct sunlight.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

CARBON DIOXIDE AEROSOL PROPELLANT

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	5000ppm 9150mg/m ³	15000ppm 27400mg/m ³	-	-

ISOPARAFFINIC HYDROCARBON

UK	1000mg/m ³	-	-	-
----	-----------------------	---	---	---

[cont...]

SAFETY DATA SHEET
FLAWFINDER DYE PENETRANT SPRAY

Page: 4

WHITE MINERAL OIL

UK	5 mg/m3	10 mg/m3	-	-
----	---------	----------	---	---

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Respiratory protection not normally required.

Hand protection: Nitrile gloves. Neoprene gloves. PVA gloves.

Eye protection: Safety glasses with side-shields.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Aerosol

Colour: Red

Odour: Characteristic odour

Evaporation rate: Slow

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Not miscible

Viscosity: Oily

Flash point°C: 75 min

Relative density: < 1

9.2. Other information

Other information: Not applicable.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

10.4. Conditions to avoid

Conditions to avoid: Direct sunlight. Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong reducing agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

[cont...]

SAFETY DATA SHEET
FLAWFINDER DYE PENETRANT SPRAY

Page: 5

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values: Not applicable.

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: Not applicable.

12.2. Persistence and degradability

Persistence and degradability: Only slightly biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Non-volatile. Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This substance is not identified as a PBT substance.

12.6. Other adverse effects

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1950

14.2. UN proper shipping name

Shipping name: AEROSOLS, Flammable

14.3. Transport hazard class(es)

Transport class: 2

[cont...]

SAFETY DATA SHEET
FLAWFINDER DYE PENETRANT SPRAY

Page: 6

14.4. Packing group

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

Safety data sheet prepared in accordance with Commission Directive 2008/47/EC of 8 April 2008 amending, for the purposes of adapting to technical progress, Council Directive 75/324/EEC relating to aerosol dispensers
Compiled in accordance with REACH.

Phrases used in s.2 and 3: None

R12: Extremely flammable.

R20: Harmful by inhalation.

R65: Harmful: may cause lung damage if swallowed.

R66: Repeated exposure may cause skin dryness or cracking.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.