Data sheet

Commercial Art.No.: 78.930.0453.0

modular insert FLE SRC 4 40

Modular connector system RJ 45 male contact 30V/1A, Cat 5, ?100 Mbit/s + 4 female contacts 400V/10A / 4 POF



Commercial Art.No.	78.930.0453.0
EAN	4015573821972
Order Unit	5

certificates / approvals

Technical data

general

model	pin insert
inflammability class of insulation material acc. with UL94	V0
color	grey
mating cycles	50
pollution degree	3
suitable for modular version	yes
operating temperature range min.	-20 °C
operating temperature range max.	80 °C

connection data

connection type	other
number of poles	8
plus switching contacts	0
number of pole for rated current 2	4
number of pole for rated current 3	0
total number of poles (without ground contact)	12
with wire protection	no
protective contact	no

technical data UL/CSA

min. conductor cross section flexible wire	0.14 mm²
max. conductor cross section flexible wire	2.5 mm²

conductor cross section flexible AWG wire	26-14 AWG

model

with housing	no

contacts

contact material	copper alloy
surface	gilt

technical data DIN EN 61984

nominal voltage	30 V
nominal voltage 2	400 V
nominal current	1 A
nominal current 2	10 A
rated impulse voltage	0.5 kV

classification

ECLASS 11	
ECLASS 8.1	27440205
ETIM 9.0	EC000438
ETIM 8.0	EC000438
ETIM 7.0	EC000438
ETIM 6.0	EC000438
ETIM 5.0	EC000438
ETIM 4.0	EC000438
ETIM 3.0	EC000438


product compliance


ROHS conformity status	compliant
REACH-SVHC conformity status	compliant


Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.


These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig









1:1

Für Steckerkontakte Ø1,6 mm (nicht im Lieferumfang enthalten) /for connector contacts Ø1,6 mm (not included in delivery)	
Querschnitt / cross section	Art.Nr. / part number
0,14 - 0,37 qmm	05.544.4129.8
0,5 qmm	05.544.4229.8
0,75 - 1,0 qmm	05.544.4329.8
1,5 qmm	05.544.4429.8
2,5 qmm	05.544.4529.8

Zulassungen /approvals	
Bemessungsspannung Daten /data rated voltage Power	30V 230V/400V
Bemessungsstrom Daten /data rated current Power	1A 10A
Verschmutzungsgrad /pollution degree	3
Datenübertragungsrate /data transmission rate	<100 Mbit/s
Übertragungsverhalten /transfer behaviour	gemäß Category 5 /subject to category 5
Kontaktdurchmesser /contact diameter	1,6 mm / 02.125.41-4529.8
Isoliergehäuse /insulating housing	PA 6.6 glasfaserverstärkt, halogenfrei /PA 6.6 fiberglas reinforced, halogen free
Brennbarkeitsklasse /flammability rating	UL94 V-0
Farbe /colour	grau ähnlich RAL 7032 /grey similar to RAL 7032
Betriebstemperaturbereich /operating temperature range	-20°C - +80°C

Weitere Daten siehe Katalog oder eKatalog /additional data see catalog or eCatalog
www.wieland-electric.com
esho.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envolope principle. According to the envolope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1
Sheet: 1 of 1

	/	Werkstoff / Material		Tag/Date	Name	Zeichnung Nr. / Drawing No. 78.930.0453.0 13K Index f
	/		gezeichnet drawn	02.11.2022	Österling	
	/	Maßstab / Scale 2:1	Elektronische Freigabe Electronic Release			
	/		Maße in mm / Dimensions are in mm			
	/	Vol. mm³ Ofl./Srf. mm²	Ersatz für / Replacement for:			
f	30.11.2022 /	wieland	Type FLE SRC 4 40	Benennung/Title Moduleinsatz_ST module insert		
e	02.11.2022 /					
Index	Datum / Blatt Date / Sheet					
Änderung / Revision						