

Features

- Heavy Duty
- Industrial castor
- Rotation Swivel
- Fixing Plate
- Polyamide 6
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing
- Breake

RS PRO Castor Wheels

RS Stock No.: 0149233



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description









Heavy polyamide 6 wheel. Hub on roller bearings, shielded ball bearings assembled with central spacer. In zinc-chromium plated pressed steel, high thickness, turning on double rim of balls fitted in temperate thrust-bearings. Dust cover ring on the balls..

General Specifications

Rotation	Swivel
Weight Class	Heavy Duty
Load Capacity (Kg)	800
Load Capacity / 4pcs (Kg)	3200
Tyre Material	Polyamide 6
Hub Material	Polyamide 6
Bracket Material	Pressed Steel
Includes Brake	Yes
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Industrial castor

Operation Environment Specifications

Operating Temperature (Celsius)	-25° to 85°
---------------------------------	-------------

							
200x57	135x110	105x80	13x16	57	251	800	1000

Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	200
Wheel / Tread Width (mm)	57
Overall Height (mm)	251
Number of Fixing Holes	4
Fixing Hole Size (mm)	11x16
Hub Bearing Type	Ball Bearing
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	
Levelling Extent (mm)	
Offset (mm)	57
Castor Weight (Kg)	1.506

Fixing Centres Specifications

Fixing Centres (mm)	105x80
Fixing Centres Length (mm)	105
Fixing Centres Width (mm)	80

Fixing Plate Specifications

Fixing Plate Dimensions (mm)	135x110
Fixing Plate Length (mm)	135
Fixing Plate Width (mm)	110