

# HN 21-22

## SKF Hook spanner, size 21-22



The SKF Hook spanner, size 21 - 22, is designed for easy tightening and loosening of lock nuts. They are used to secure and adjust bearings on tapered journals, adapter sleeves and withdrawal sleeves. They fit on a variety of lock nuts with outer diameter(s) 135 - 145 mm. To be more specific for locknuts: KM 21, KM 22, KMFE 21, KMFE 22, KMT 20, KMT 22, AN 21, AN 22 and M95x2, M100x2 (DIN 1804).

- Optimised design allow use in narrow spaces while maintaining maximum force
- Sturdy plastic handle that is oil, dirt and grease resistant to provide a better grip
- Drilled hole for easy hanging storage
- Laser-engraved designation for easy identification
- They fit on a variety of locknuts with outer diameter(s) 135 - 145mm

## Overview

### Dimensions

Outer diameter locknut range, d	135-145 mm
Outer diameter lock nut range	135 to 145 mm
Working length	12.598 in
Thickness	0.472 in
Length	15.197 in
Product weight	2.668 lb

## Properties

Allows bearing mounting	no
Coating	Black phosphated
Colour	Black, with red handle
Fits on lock nuts inside SKF split pillow block housings (SNL)	no
Material	Medium carbon steel, hardened and tempered
Material handle	Durable soft plastic
Part of a kit	no

Spanner following  
DIN 1810 size

135-145 mm

Allows bearing  
mounting

No

Fits on lock nuts inside  
SKF split  
pillow block housings  
(SNL)

No

Spanner following  
DIN 1810 size

135 to 145 mm

Material

Medium carbon steel, hardened and  
tempered

Part of a kit

No

Material handle

Durable soft plastic

Coating

Black phosphated

Colour

Black, with red handle

# Terms and conditions

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 - Gothenburg) ("SKF"), you agree to the following terms and conditions:

## Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app. Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service. Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

## Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using YouTube API Services), you agree to be bound by the YouTube Terms of Service.

## Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website / app includes certain images used under license from Shutterstock, Inc.

## Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

## Changes

SKF reserves the right to make changes or additions to this website / app at any time.