



Brand of NTN corporation

## Technical data



### 6306NR

Single row deep groove ball bearings



Deep groove ball bearing, radial contact, pressed steel cage, snap ring & groove on outer diameter, open

#### VISUAL (S)



#### NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

## PRODUCT DEFINITION

|                                                           |          |
|-----------------------------------------------------------|----------|
| <b>Brand</b>                                              | SNR      |
| <b>d - Internal diameter</b>                              | 30 mm    |
| <b>D - External diameter</b>                              | 72 mm    |
| <b>B - Bearing/Inner ring width</b>                       | 19 mm    |
| <b>d1 - External diameter inner ring</b>                  | 41,7 mm  |
| <b>D1 - Inner diameter outer ring</b>                     | 62,5 mm  |
| <b>a min - Min position Groove</b>                        | 3,07 mm  |
| <b>a max - Max position groove</b>                        | 3,28 mm  |
| <b>Ca min - Mini segment position</b>                     | 4,67 mm  |
| <b>Ca max - Max segment position</b>                      | 4,98 mm  |
| <b>rs - Min fillet radius</b>                             | 1,1 mm   |
| <b>rNs - Min fillet radius</b>                            | 0,5 mm   |
| <b>D3 - Max bottom groove diameter</b>                    | 68,81 mm |
| <b>b min - Min groove width</b>                           | 1,9 mm   |
| <b>b max - Max groove width</b>                           | 2,2 mm   |
| <b>r0 max - Max bottom groove radius</b>                  | 0,6 mm   |
| <b>D4 max - Max outer diameter of assembled stop ring</b> | 78,6 mm  |
| <b>f - Stop ring thickness</b>                            | 1,65 mm  |
| <b>Snap ring reference</b>                                | R72      |
| <b>Radial clearance class</b>                             | CN       |
| <b>Mass</b>                                               | 0,346 kg |

## PRODUCT PERFORMANCE

|                         |             |
|-------------------------|-------------|
| <b>C - Dynamic load</b> | 29700000 mN |
|-------------------------|-------------|



# 6306NR

Single row deep groove ball bearings

## PRODUCT PERFORMANCE

|                                         |             |
|-----------------------------------------|-------------|
| <b>C0 - Static load</b>                 | 15900000 mN |
| <b>Cu - Fatigue limit load</b>          | 720000 mN   |
| <b>f0 - Coefficient</b>                 | 13.1        |
| <b>N ref - Reference thermal speed</b>  | 66000 °/s   |
| <b>N lim - Mechanical Limit Speed</b>   | 96000 °/s   |
| <b>Tmin - Min operating temperature</b> | 233,15 °K   |
| <b>Tmax - Max operating temperature</b> | 393,15 °K   |

## BEARING FREQUENCIES

|                                                                 |          |
|-----------------------------------------------------------------|----------|
| <b>BPFO - Over rolling frequency on outer ring (60 rpm)</b>     | 3.054 Hz |
| <b>BPFI - Over rolling frequency on inner (60 rpm)</b>          | 4.946 Hz |
| <b>BSF - Over rolling frequency on rolling element (60 rpm)</b> | 3.99 Hz  |
| <b>BRF - Rotational frequency - rolling element (60 rpm)</b>    | 1.995 Hz |
| <b>FTF - Rotational frequency - cage (60 rpm)</b>               | 0.382 Hz |

## ABUTMENT

|                                                       |         |
|-------------------------------------------------------|---------|
| <b>da min - Min shoulder diameter IR</b>              | 36,5 mm |
| <b>Da max - Max shoulder diameter OR</b>              | 65,5 mm |
| <b>ra max - Max shaft &amp; housing fillet radius</b> | 1 mm    |
| <b>rNa max - Max fillet radius on segment side</b>    | 0,5 mm  |
| <b>Db min - Min stop ring position diameter</b>       | 80 mm   |



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

| $\frac{f_0 F_a}{C_0}$ | e    | Fa / Fr ≤ e |   | Fa / Fr > e |      |
|-----------------------|------|-------------|---|-------------|------|
|                       |      | X           | Y | X           | Y    |
| 0.172                 | 0.19 | 1           | 0 | 0.56        | 2.3  |
| 0.345                 | 0.22 |             |   |             | 1.99 |
| 0.689                 | 0.26 |             |   |             | 1.71 |
| 1.03                  | 0.28 |             |   |             | 1.55 |
| 1.38                  | 0.3  |             |   |             | 1.45 |
| 2.07                  | 0.34 |             |   |             | 1.31 |
| 3.45                  | 0.38 |             |   |             | 1.15 |
| 5.17                  | 0.42 |             |   |             | 1.04 |
| 6.89                  | 0.44 |             |   |             | 1    |

Equivalent static radial load

$P_0 = X_0.F_r + Y_0.F_a$

| X <sub>0</sub> | Y <sub>0</sub> |
|----------------|----------------|
| 0.6            | 0.5            |

For single or DT bearing arrangement :

If P<sub>0</sub> <F<sub>r</sub>, then use P<sub>0</sub> = F<sub>r</sub>

