



## Main

Range of product	Canalis
Range compatibility	Canalis KN busbar trunking
Product or component type	Tap-off unit
Busbar trunking compatibility	Canalis KN busbar trunkingplug-in
[Ie] rated operational current	20 A at 35 °C
Protection type	Fuse isolator: BS88 fuse, size A1 conforming to BS
Provided equipment	Fuse to be ordered separately Cable clamp
Mounting mode	Plug-in with fixed polarity
Tap-off unit polarity	3L+PE 3L+N+PE
Colour	White (RAL 9001)

## Complementary


Device application	Low power distribution
[Ue] rated operational voltage	230...500 V depending on protective device
[Uimp] rated impulse withstand voltage	4.6 kV
[Ui] rated insulation voltage	500 V depending on protective device
Network frequency	50/60 Hz
Electrical connection	Cable clamp terminal - ISO32 4 mm² flexible Cable clamp terminal - ISO32 6 mm² rigid
Door/cover opening side	Front
Tap-off unit disconnection mode	By drawing out
Standards	IEC 61439-1 IEC 61439-6
Width	135 mm
Depth	90 mm
Height	165 mm
Net weight	0.6 kg

## Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins