



571

ORASOLV B60

MULTIPURPOSE SOLVENT

SAFETY FLASH POINT
TYPE A3 SOLVENT



BENEFITS

- Does not contain recycled solvents.
- Very economical waste treatment by the ORAPI sector.
- 70% biodegradable in 28 days according to OECD 301F standard.
- Complies with new Community regulations (without chlorinated or fluorinated solvents) and free from aromatic compounds.
- Rapid evaporation by blowing.
- High flash point ensuring user safety.
- Penetrates deeply and perfectly dissolves greasy and oily deposits.
- Does not cause oxidation of ferrous metals after drying.
- Without blowing, it leaves a light anti-corrosion greasy film which is very popular for inter-machining operations



02100220 (5 l)
02107205 (20 l)
82100250 (200 l)



DEFINITION

Solvent synthesized from very high quality refined hydrocarbons for efficient degreasing.

INSTRUCTIONS FOR USE

Can be used pure and cold: cleaning with a brush, cloth, soaking, in an ultrasonic tank or fountain.

Particularly suitable for use with our degreasing fountains equipped with non-priming pumps.

Electric fountain for 200 l barrel	ref. 700050
Pneumatic fountain for 200 l barrel	ref. 700051

FIELD OF APPLICATION

Specially adapted for the rapid and complete degreasing of all mechanical parts and metal surfaces: cleaning of engine blocks, gasket faces, windings of electric motors (dismantled).

ORAPI® cannot be aware of all the applications in which its products are used and the conditions of their use. ORAPI® assumes no responsibility for: the suitability of its products for a given use or for a particular purpose, the application methods over which it has no control. The information contained in this technical data sheet must in no case replace the preliminary tests that must be carried out to verify the suitability of the product for each intended application. The user of the product described in this technical data sheet remains solely responsible for all measures required to protect people and property against all risks that may result from the implementation and/or use of this product. Consequently, ORAPI® disclaims all implied or explicit warranties, including warranties relating to the fitness for sale or suitability for a particular need, resulting from the sale or use of its products. ORAPI® specifically denies any prosecution for incidental or consequential damages of any kind, including financial operating losses.



571

ORASOLV B60

MULTIPURPOSE SOLVENT

SAFETY FLASH POINT
TYPE A3 SOLVENT

FEATURES

Aspect :	Clear liquid
Color :	Colorless
Smell :	Characteristic
Density at 20°C:	0.79
Flash point:	> 61°C
Evaporation rate:	0.2
Dielectric strength:	> 40 000 V
Aromatic content:	< 0.1%
Point d'aniline :	About 72°C

PACKAGING

1000 l cubes	ref.2571N1	x1
200 l barrel	ref.2571U2	x1
60 l barrel	ref.2571O5	x1
20 l barrel	ref.2571O1	x1
Jerrican 5 l	ref.2571J1 SNCF	x1
1 l can	ref.2571I2	x12



ORAPI® cannot be aware of all the applications in which its products are used and the conditions of their use. ORAPI® assumes no responsibility for: the suitability of its products for a given use or for a particular purpose, the application methods over which it has no control. The information contained in this technical data sheet must in no case replace the preliminary tests that must be carried out to verify the suitability of the product for each intended application. The user of the product described in this technical data sheet remains solely responsible for all measures required to protect people and property against all risks that may result from the implementation and/or use of this product. Consequently, ORAPI® disclaims all implied or explicit warranties, including warranties relating to the fitness for sale or suitability for a particular need, resulting from the sale or use of its products. ORAPI® specifically denies any prosecution for incidental or consequential damages of any kind, including financial operating losses.