

# REVIE FLEX 700

Flexible 5G, 4G/LTE, Cat M1, NB-IoT Antenna 698-960 MHz/1350-1610 MHz/1690-2180 MHz/ 2300-2700 MHz/3300-4200 MHz/4900-6000 MHz

### LAIRD CONNECTIVITY IS AN AUTHORITY

#### IN CUSTOMER ANTENNA INTEGRATION SUPPORT



The Revie 700 peel-and-stick flexible adhesive-backed antenna measures only 96 x 21 mm and delivers over 45% efficiency over the 698-6000 MHz frequency range. It is ideal for 5G devices designed for use on the largest mobile carrier networks that often do not use the lowest frequency bands.

#### FEATURES AND BENEFITS

#### **APPLICATIONS**

- Optimized performance for sub-6 GHz 5G
- Ground Plane Independent
- High efficiency for ease of carrier certification
- 5G NR devices
- LTE-M, Cat M, Cat M1, NB-IoT
- CBRS, GNSS bands supported.

ELECTRICAL SPECIFICATIONS												
Laird Connectivity Part Number	EFF6989A3S-19MHF1											
Operating Frequency (MHz)	698-824	824-894	880-960	1350-1550	1550-1690	1690-1880	1850-1990	1910-2170	2300-2500	2500-2700	3300-4200	4900-6000
Gain (dBi) – Avg	0.5	0.9	2.0	3.7	4.1	3.6	3.5	3.7	3.4	3.0	2.4	4.0
Gain (dBi) – Max	0.9	1.4	2.7	4.0	4.2	4.1	3.7	3.9	3.7	3.5	3.3	4.5
Efficiency (%) – Avg	50	46	46	71	75	81	84	83	75	69	64	68
Efficiency (dB) – Avg	-3.00	-3.40	-3.40	-1.50	-1.30	-0.90	-0.80	-0.80	-1.30	-1.60	-2.00	-1.70
VSWR – Avg	2.1	2.4	2.0	2.3	1.9	1.8	1.7	1.4	1.7	2.1	1.7	1.5
VSWR – Max	<2.5				<2.0				<2.5		<2.2	
Nominal Impedance (Ohms)	50											
Polarization	Linear vertical											
Azimuth Beamwidth	360°, Omnidirectional											
Input Power (W) – Max	5											

**Note:** Measured on a 1.7 mm thick polycarbonate sheet.

A minimum cable length of 190 mm is required to achieve the stated efficiency.

MECHANICAL SPECIFICATIONS	
Dimensions – L x W x H – mm (inches)	96.0 x 21.0 x 0.2 (3.78 x 0.83 x 0.008)
Connector	U.FL / MHF1 or equivalent
Cable Type	Coax 1.13 (gray color)
Cable Exposed Length – mm (in.)	190 ± 5 (7.48 ± 0.2)
Flexible Circuit material	Polyimide (black masking)

ENVIRONMENTAL SPECIFICATIONS	
Operating Temperature – °C (°F)	-40 to +85°C (-40 to +185°F)
Storage Temperature – °C (°F)	-40 to +85°C (-40 to +185°F)
Material Substance Compliance	RoHS

#### CONFIGURATION


PART NUMBER	EXPOSED CABLE LENGTH	CONNECTOR	PACKAGING
EFF6989A3S-19MHF1	190 ± 5 mm (7.48 ± 0.2 in.)	MHF1 / U.FL or equivalent	20 pieces / bag
EFF6989A3S-19MH4L	190 ± 5 mm (7.48 ± 0.2 in.)	IPEX MHF4L	20 pieces / bag


#### PACKAGING INFORMATION

	BAG	CARTON		MASTE	R PACK	AIR PALLET	OCEAN PALLET	
Number of Antennas	20 antennas	10 bags	10 bags 200 antennas		1600 antennas	28,800	38400	
Dimensions – mm (in.)	209.6 x 187.5 (8.25 x 7.38)	250 x 125 x 145 (9.84 x 4.92 x 5.71)		526 x 305 x 266 (20.71 x 12.01 x 10.47)		1200 x 800 x 1024 (47.24 x 31.5 x 40.31)	1200 x 800 x 1325 (47.24 x 31.5 x 52.17)	
Weight – kg (lb.)	0.037 (0.108)	0.47 (1.03)		4.38 (9.66)				




#### MECHANICAL DRAWING







#### **VSWR**



#### **TOTAL EFFICIENCY (%)**



#### MAX GAIN (dBi)





150

210

150

210


180


270

180


## **REVIE FLEX 700** Flexible 5G, 4G/LTE, Cat M1, NB-IoT Antenna


#### **RADIATION PATTERNS**














1730 MHz Phi 0° Plane





180



Phi 90° Plane

-15 -20 -25 -30

180

-20 -25 -30 -35

180

150


150


180

180


210

210







849 MHz




1448 MHz Phi 0° Plane







Phi 90° Plane

2140 MHz












### **REVIE FLEX 700** Flexible 5G, 4G/LTE, Cat M1, NB-IoT Antenna

#### **RADIATION PATTERNS**



240

210

180

sales@lairdconnect.com support@lairdconnect.com www.lairdconnect.com 210

270

© Copyright 2022 Laird Connectivity. All Rights Reserved. Patent pending. Any information furnished by Laird Connectivity and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Connectivity materials or products rests with the end user since Laird Connectivity and its agents cannot be aware of all potential uses. Laird Connectivity materials or products rests with the end user since Laird Connectivity materials or products for any specific or general uses. Laird Connectivity on any of its affiliates or agents shall not be liable for incidential or consequential damages of any kind. All Laird Connectivity products are sold pursuant to the Laird Connectivity or sold and the set of any connectivity or any third-party intellectual property right.

120

150

240

210

150

180