



Main

| | |
|---------------------------|---------|
| Range of product | TeSys G |
| Range | TeSys |
| Device short name | LA9G |
| Product or component type | Plate |
| Range compatibility | TeSys G |
| Product compatibility | LR9G630 |
| Poles description | 3P |

Complementary

| | |
|------------------|----------|
| Height | 13.5 mm |
| Width | 210 mm |
| Depth | 51.7 mm |
| Net weight | 0.065 kg |
| Quantity per set | Set of 1 |

Environment

| | |
|---------------------------------------|--|
| IP degree of protection | IP20 conforming to IEC 60529 |
| Ambient air temperature for operation | -25...60 °C |
| Ambient air temperature for storage | -60...80 °C |
| Pollution degree | 3 conforming to IEC 60947-1 |
| Operating altitude | 3000 m without derating 5000 m with derating factor |
| Standards | EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 GB/T 14048.4 |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |