

Vacuum Cleaner LXT®

DCL181F

18V • 53 mbar • 0,65 l

This silent vacuum cleaner, with high suction power and two power settings, is ideal for removing dirt and dust from the floor, staircases, jobsite or vehicle.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Air volume	1,4 m³/min
Max. sealed suction	42 mbar
Continuous Use 18V / 5.0 Ah Battery	33 min
Tank Capacity for Dust	0,65 L
Sound Pressure Level (L _{pA})	61,1 / 72,2 dB(A)
Tool weight with battery	1,2 - 1,4 kg
Product Dimensions (L x W x H):	999 x 114 x 152 mm
Continuous Use 18V / 3.0 Ah Battery	40 / 20 min
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Suction power	11 / 30 W
Product net weight	0,8 kg

User benefits

- Low noise level for pleasant work.
- Ideal for upholstered furniture and stairs or workshop use
- Ergonomic soft grip handle provides increased comfort
- Battery protection system automatically shuts off power when the battery level is low
- Increased storage capacity for longer time between waste disposal

Link to product - www.makitauk.com



Related products

Optional AC

1910D3-4

Cyclone Pre-separator, White



1910D4-2

Cyclone Pre-separator



1910D5-0

Cyclone Pre-separator



191496-7

Flexible Hose



191D67-4

Round brush



191M30-1

Brush Nozzle



Other

User manual

Parts drawing