

## dsPIC33FJ64GS610 100-pin TQFP to 100-pin Plug-In Module (PIM) Information Sheet

### OVERVIEW

The dsPIC33FJ64GS610 PIM is designed to demonstrate the capabilities of the dsPIC33FJ64GS610 family of Switch Mode Power Supply (SMPS) devices using the Explorer 16 Development Board and the PICtail™ Plus Daughter Board.

The dsPIC33FJ64GS610 is a high-performance 16-bit Digital Signal Controller in a 100-pin TQFP package.

Table 1 shows the mapping between the 100-pin PIM interface board functions and the device pins.

**TABLE 1: 100-PIN TQFP TO 100-PIN PIM PINOUT**

Device Pin Number	dsPIC33FJ64GS610 Pin	PIM Pin Number	Functional Description
1	SYNCI1/RG15	—	
2	VDD	2	
3	PWM3H/RE5	19	PWM3H
4	PWM4L/RE6	—	
5	PWM4H/RE7	—	
6	AN16/T2CK/RC1	17	LED3
7	AN17/T3CK/RC2	38	LED4
8	AN18/T4CK/RC3	58	LED5
9	AN19/T5CK/RC4	59	LED6
10	SCK2/FLT12/CN8/RG6	—	
11	SDI2/FLT11/CN9/RG7	—	
12	SDO2/FLT10/CN10/RG8	—	
13	MCLR	13	
14	SS2/FLT9/CN11/RG9	—	
15	Vss	15	
16	VDD	16	
17	TMS/RA0	—	
18	AN20/FLT13/INT1/RE8	—	
19	AN21/FLT14/INT2/RE9	—	
20	AN5/CMP3B/QEB1A/CN7/RB5	20	Exp_ POT
21	AN4/CMP2C/CMP3A/QEA1A/CN6/RB4	66	VIN_Feedback
22	AN3/CMP2B/INDX1A/CN5/RB3	57	Voltage FB2
23	AN2/CMP1C/CMP2A/SS1A/CN4/RB2	56	Current Sense 2
24	PGEC3/AN1/CMP1B/CN3/RB1	35	Voltage FB1
25	PGED3/AN0/CMP1A/CMP4C/CN2/RB0	34	Current Sense 1
26	PGEC1/AN6/CMP3C/CMP4A/OCFA/RB6	26	PGEC1
27	PGED1/AN7/CMP4B/RB7	27	PGED1
28	PWM8L/RA9	—	
29	PWM8H/RA10	—	
30	AVDD	30	

# dsPIC33FJ64GS610

**TABLE 1: 100-PIN TQFP TO 100-PIN PIM PINOUT (CONTINUED)**

Device Pin Number	dsPIC33FJ64GS610 Pin	PIM Pin Number	Functional Description
31	AVss	31	
32	AN8/RB8	69	Current Sense Boost
33	AN9/DACOUT/RB9	78	Voltage Feedback Boost
34	AN10/RB10	68	POT
35	AN11/EXTREF/RB11	—	
36	Vss	36	
37	VDD	37	
38	TCK/RA1	—	
39	U2RTS/RF13	—	
40	U2CTS/RF12	—	
41	AN12/CMP1D/RB12	—	
42	AN13/CMP2D/RB13	—	
43	AN14/CMP3D/SS1/RB14	—	
44	AN15/CMP4D/OCFB/CN12/RB15	44	LCD (R/S)
45	Vss	45	
46	VDD	46	
47	U1CTS/FLT15/SYNCI3/CN20/RD14	—	
48	U1RTS/FLT16/SYNCI2/CN21/RD15	—	
49	U2RX/FLT17/CN17/RF4	—	
50	U2TX/FLT18/CN18/RF5	—	
51	U1TX/RF3	50	UART TX
52	U1RX/RF2	49	UART RX
53	SDO1/RF8	—	
54	SDI1/RF7	—	
55	SCK1/INT0/RF6	—	
56	SDA1/RG3	96	SDA/RX
57	SCL1/RG2	95	SCL/TX
58	SCL2/FLT22/RA2	83	Switch S3
59	SDA2/FLT21/RA3	84	Switch S6
60	TDI/RA4	—	
61	TDO/RA5	—	
62	VDD	62	
63	OSC1/CLKIN/RC12	63	OSC1
64	OSC2/REFCLKO/CLKO/RC15	64	OSC2
65	Vss	65	
66	INT3/FLT20/RA14	—	
67	INT4/FLT19/SYNCI4/RA15	—	
68	IC1/FLT1/RD8	100	LCD (DB4)
69	IC2/FLT2/RD9	3	LCD (DB5)
70	IC3/INDX1/FLT3/RD10	4	LCD (DB6)
71	IC4/QEA1/FLT4/RD11	5	LCD (DB7)
72	OC1/QEB1/FLT5/RD0	93	LCD (DB0)
73	PGED2/SOSCI/CN1/RC13	—	
74	PGEC2/SOSCO/T1CK/CN0/RC14	—	

# dsPIC33FJ64GS610

**TABLE 1: 100-PIN TQFP TO 100-PIN PIM PINOUT (CONTINUED)**

Device Pin Number	dsPIC33FJ64GS610 Pin	PIM Pin Number	Functional Description
75	Vss	75	
76	OC2/SYNCO2/FLT6/RD1	94	LCD (DB1)
77	OC3/FLT7/RD2	98	LCD (DB2)
78	PWM7H/OC4/FLT8/RD3	99	LCD (DB3)
79	QEA2/RD12	—	
80	PWM7L/CN19/RD13	—	
81	PWM6L/CN13/RD4	81	LCD (E)
82	PWM6H/CN14/RD5	82	LCD (R/W)
83	PWM5L/CN15/RD6	—	
84	PWM5H/UPDN1/CN16/RD7	—	
85	VCAP/VDDCORE	—	
86	VDD	86	
87	C1RX/RF0	1	PMBAUX1
88	C1TX/RF1	97	PMBAUX2
89	QEB2/RG1	—	
90	INDX2/RG0	—	
91	AN22/CN22/RA6	—	
92	AN23/CN23/RA7	—	
93	PWM1L/RE0	29	PWM1L
94	PWM1H/RE1	28	PWM1H
95	FLT23/RG14	—	
96	PWM9H/RG12	—	
97	PWM9L/RG13	—	
98	PWM2L/RE2	25	PWM2L
99	PWM2H/RE3	24	PWM2H
100	PWM3L/RE4	22	LOAD





# dsPIC33FJ64GS610

---

NOTES:

---

**Note the following details of the code protection feature on Microchip devices:**

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as “unbreakable.”

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

---

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights.

**Trademarks**

The Microchip name and logo, the Microchip logo, dsPIC, KEELOQ, KEELOQ logo, MPLAB, PIC, PICmicro, PICSTART, rPIC and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.


FilterLab, Hampshire, HI-TECH C, Linear Active Thermistor, MXDEV, MXLAB, SEEVAL and The Embedded Control Solutions Company are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Application Maestro, CodeGuard, dsPICDEM, dsPICDEM.net, dsPICworks, dsSPEAK, ECAN, ECONOMONITOR, FanSense, HI-TIDE, In-Circuit Serial Programming, ICSP, Mindi, MiWi, MPASM, MPLAB Certified logo, MPLIB, MPLINK, mTouch, Octopus, Omniscient Code Generation, PICC, PICC-18, PICDEM, PICDEM.net, PICkit, PICtail, PIC<sup>32</sup> logo, REAL ICE, rLAB, Select Mode, Total Endurance, TSHARC, UniWinDriver, WiperLock and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

All other trademarks mentioned herein are property of their respective companies.

© 2009, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

 Printed on recycled paper.

**QUALITY MANAGEMENT SYSTEM**  
**CERTIFIED BY DNV**  
**== ISO/TS 16949:2002 ==**

*Microchip received ISO/TS-16949:2002 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.*



---

---

## Worldwide Sales and Service

---

---

### AMERICAS

**Corporate Office**  
2355 West Chandler Blvd.  
Chandler, AZ 85224-6199  
Tel: 480-792-7200  
Fax: 480-792-7277  
Technical Support:  
<http://support.microchip.com>  
Web Address:  
[www.microchip.com](http://www.microchip.com)

**Atlanta**  
Duluth, GA  
Tel: 678-957-9614  
Fax: 678-957-1455

**Boston**  
Westborough, MA  
Tel: 774-760-0087  
Fax: 774-760-0088

**Chicago**  
Itasca, IL  
Tel: 630-285-0071  
Fax: 630-285-0075

**Cleveland**  
Independence, OH  
Tel: 216-447-0464  
Fax: 216-447-0643

**Dallas**  
Addison, TX  
Tel: 972-818-7423  
Fax: 972-818-2924

**Detroit**  
Farmington Hills, MI  
Tel: 248-538-2250  
Fax: 248-538-2260

**Kokomo**  
Kokomo, IN  
Tel: 765-864-8360  
Fax: 765-864-8387

**Los Angeles**  
Mission Viejo, CA  
Tel: 949-462-9523  
Fax: 949-462-9608

**Santa Clara**  
Santa Clara, CA  
Tel: 408-961-6444  
Fax: 408-961-6445

**Toronto**  
Mississauga, Ontario,  
Canada  
Tel: 905-673-0699  
Fax: 905-673-6509

### ASIA/PACIFIC

**Asia Pacific Office**  
Suites 3707-14, 37th Floor  
Tower 6, The Gateway  
Harbour City, Kowloon  
Hong Kong  
Tel: 852-2401-1200  
Fax: 852-2401-3431

**Australia - Sydney**  
Tel: 61-2-9868-6733  
Fax: 61-2-9868-6755

**China - Beijing**  
Tel: 86-10-8528-2100  
Fax: 86-10-8528-2104

**China - Chengdu**  
Tel: 86-28-8665-5511  
Fax: 86-28-8665-7889

**China - Hong Kong SAR**  
Tel: 852-2401-1200  
Fax: 852-2401-3431

**China - Nanjing**  
Tel: 86-25-8473-2460  
Fax: 86-25-8473-2470

**China - Qingdao**  
Tel: 86-532-8502-7355  
Fax: 86-532-8502-7205

**China - Shanghai**  
Tel: 86-21-5407-5533  
Fax: 86-21-5407-5066

**China - Shenyang**  
Tel: 86-24-2334-2829  
Fax: 86-24-2334-2393

**China - Shenzhen**  
Tel: 86-755-8203-2660  
Fax: 86-755-8203-1760

**China - Wuhan**  
Tel: 86-27-5980-5300  
Fax: 86-27-5980-5118

**China - Xiamen**  
Tel: 86-592-2388138  
Fax: 86-592-2388130

**China - Xian**  
Tel: 86-29-8833-7252  
Fax: 86-29-8833-7256

**China - Zhuhai**  
Tel: 86-756-3210040  
Fax: 86-756-3210049

### ASIA/PACIFIC

**India - Bangalore**  
Tel: 91-80-3090-4444  
Fax: 91-80-3090-4080

**India - New Delhi**  
Tel: 91-11-4160-8631  
Fax: 91-11-4160-8632

**India - Pune**  
Tel: 91-20-2566-1512  
Fax: 91-20-2566-1513

**Japan - Yokohama**  
Tel: 81-45-471- 6166  
Fax: 81-45-471-6122

**Korea - Daegu**  
Tel: 82-53-744-4301  
Fax: 82-53-744-4302

**Korea - Seoul**  
Tel: 82-2-554-7200  
Fax: 82-2-558-5932 or  
82-2-558-5934

**Malaysia - Kuala Lumpur**  
Tel: 60-3-6201-9857  
Fax: 60-3-6201-9859

**Malaysia - Penang**  
Tel: 60-4-227-8870  
Fax: 60-4-227-4068

**Philippines - Manila**  
Tel: 63-2-634-9065  
Fax: 63-2-634-9069

**Singapore**  
Tel: 65-6334-8870  
Fax: 65-6334-8850

**Taiwan - Hsin Chu**  
Tel: 886-3-6578-300  
Fax: 886-3-6578-370

**Taiwan - Kaohsiung**  
Tel: 886-7-536-4818  
Fax: 886-7-536-4803

**Taiwan - Taipei**  
Tel: 886-2-2500-6610  
Fax: 886-2-2508-0102

**Thailand - Bangkok**  
Tel: 66-2-694-1351  
Fax: 66-2-694-1350

### EUROPE

**Austria - Wels**  
Tel: 43-7242-2244-39  
Fax: 43-7242-2244-393

**Denmark - Copenhagen**  
Tel: 45-4450-2828  
Fax: 45-4485-2829

**France - Paris**  
Tel: 33-1-69-53-63-20  
Fax: 33-1-69-30-90-79

**Germany - Munich**  
Tel: 49-89-627-144-0  
Fax: 49-89-627-144-44

**Italy - Milan**  
Tel: 39-0331-742611  
Fax: 39-0331-466781

**Netherlands - Drunen**  
Tel: 31-416-690399  
Fax: 31-416-690340

**Spain - Madrid**  
Tel: 34-91-708-08-90  
Fax: 34-91-708-08-91

**UK - Wokingham**  
Tel: 44-118-921-5869  
Fax: 44-118-921-5820



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microchip:](#)

[MA330024](#)