



Switches > Slide Switches



Contact Current Rating: **.3 A**

Configuration (Pole-Throw): **Single Pole - Double Throw**

Contact Base Material: **Copper Alloy**

Number of Actuators: **Single**

Number of Positions: **2**

Features

Configuration Features

Terminals Connected	2-1
Configuration (Pole-Throw)	Single Pole - Double Throw
Number of Actuators	Single
Number of Positions	2
Operating Function	On None On

Electrical Characteristics

Contact Current Rating	.3 A
------------------------	------

Body Features

Actuator Orientation	Side
Actuator Travel	2 mm[.079 in]
Actuator Material	POM
Actuator Color	Black

Contact Features

Contact Base Material	Copper Alloy
Switch Contact Plating Material	Silver

Termination Features

Termination Post & Tail Length	3.68 mm[.145 in]
Termination Method to PCB	Through Hole - Solder

Dimensions



Product Width	5.6 mm[.221 in]
Product Length	18 mm[.709 in]
Actuator Length	4 mm[.157 in]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Tray
------------------	------

Other

Grade	Instrumentation
-------	-----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.



Customers Also Bought

 TE Part #5-104319-2 20 MODII HDR DRRA SHRD LF	 TE Part #1-328690-2 JAM NUT, GOLD PLATED	 TE Part #6-747844-9 9P RA MSFL 318 RCPT	 TE Part #3-1546159-1 6WWV-11-008=#6 TRIBARRIER TERM
 TE Part #6-1825011-4 ASF62RG04=6PDT AUTOSLIDE	 TE Part #1986563-4 SSB7TP040402=TERM BLOCK ASSY	 TE Part #2-330312-2 MINIATURE THREADED RECEPTACLES	 TE Part #2-796608-3 6WWV-15-008=#6 TRIBARRIER

Documents

Product Drawings

MSS1200R04=SPDT SL SW R/A AG

English

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English