





PART NUMBER	149706	149707	149705	149708	149601	149709	149710	
WT 22 series Stroke length	50	75	100	150	200	250	300	Tol.
Electrical stroke length	50	75	100	150	200	250	300	±5.0
Mechanical stroke length	55	80	105	155	205	255	305	±5.0
Body length - A	146	166	166	216	266	316	366	±1.0
REB center to center- B	196	216	216	266	316	366	416	±1.0
Body diameter - D	Dia 22							±0.2
Rod end bearing-C	Both side reb							




CONDUCTIVE PLASTIC LINEAR MOTION POTENTIOMETER

MODEL WT22

FIRST ISSUE : 2016/03/08 SCALE : 1:1


TOLERANCE
DIN-ISO 2768-1 (1991-06)
(TOLERANCE CLASS-MEDIUM)




CUSTOMER DRAWING REF NO
NA

REV -00

SHEET 1 of 1



DIMENSIONS :- METRIC



ELECTRICAL SCHEMATIC DIAGRAM

STANDARD CHART FOR LINEAR POTENTIOMETER WT 22 RESISTANCE VALUE

Sr.	STROKE	RESISTANCE RANGE
1.0	50 MM	5 KΩ ± 20%
2.0	75 MM	
3.0	100 MM	
4.0	150 MM	
5.0	200 MM	10 KΩ ±20%
6.0	250 MM	
7.0	300 MM	

ELECTRICAL CHARACTERISTICS

UNITS

VALUE

RESISTANCE ELEMENT...	--	CONDUCTIVE PLASTIC
RESISTANCE TOLERANCE...	±%	20
STANDARD INDEPENDENT LINEARITY TOLERANCE...	±%	0.3
RESOLUTION...	--	ESSENTIALLY INFINITE
TEMPERATURE COEFFICIENT OF RESISTANCE(TCR)...	ppm/deg C	±400
INSULATION RESISTANCE @ 500 VDC...	M Ohms	500
DIELECTRIC STRENGTH @ 50 HZ...	V dc	500
ELECTRICAL LIFE (STROKE)...	STROKES	5,000,000
END VOLTAGE AS A % OF APPLIED VOLTAGE...	%	LESS THAN 0.5

MECHANICAL CHARACTERISTICS :-

BEARING TYPE...	--	SLEEVE
TORQUE STARTING...	Nmm (Oz inch)	10 (1.416)
TORQUE RUNNING...	Nmm (Oz inch)	5 (0.708)

ENVIRONMENTAL CHARACTERISTICS :--

OPERATING TEMPERATURE...	DEGREES C	-40 to +105
ROHS COMPLIANCE...	--	YES

MATERIALS OF CONSTRUCTION:--

HOUSING...	--	ALUMINUM BLACK ANODIZED
SHAFT...	--	STAINLESS STEEL

NOTE :-
CONTINUOUS IMPROVEMENTS ARE BEING MADE FOR ENHANCING PERFORMANCE FOR CUSTOMER BENEFIT IN PRODUCT DESIGN & PROCESS. THE PRODUCT SUPPLIED MAY BE SLIGHTLY DIFFERENT THAN DESCRIBED BY ABOVE SPECIFICATIONS