

Product datasheet

Specifications



Thalassa PHD outdoor heavy duty - aluminium cable gland plate - W500 D420

NSYPPC54HD

Main

Range	Thalassa
Product or component type	Cable gland plate
Accessory / separate part category	Cable management accessory
Application	Outdoor heavy duty
Application	Multi-purpose
Nominal width of the housing	500 mm
Nominal depth of the housing	420 mm
Range compatibility	Thalassa Thalassa PHD
Mounting location	Enclosure bottom
Type of gland plate	Plain aluminium
Device composition	fixing elements 1 plate gasket
Quantity per set	Set of 1
Material	Aluminium

Complementary

Surface finish	Brushed finish
Fixing mode	Tool less - screw type quarter-turn
Height	15 mm
Width	Nominal: 500 mm
Depth	Nominal : 420 mm Real : 510 mm
Thickness	3 mm

Packing Units


Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	43.000 cm
Package 1 Length	51.000 cm
Package 1 Weight	3.000 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications


Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)


[How we assess product sustainability >](#)

<div>Environmental footprint</div>	
Environmental Disclosure	Product Environmental Profile

Use Better

<div>Materials and Packaging</div>	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	52da316e-d4e1-4114-85c0-32a03b2934fd

Use Again

<div>Repack and remanufacture</div>	
Circularity Profile	No need of specific recycling operations
Take-back	No