


R75L, Film, Metallized Polypropylene, General Purpose, 0.1 uF, 10%, 560 VDC, 85°C, Lead Spacing = 15mm



Dimensions

L	18mm +0.3mm
H	12mm +0.1mm
T	6mm +0.2mm
S	15mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	900

General Information

Supplier:	KEMET
Series:	R75L
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Pulse, Capacitive Power Supply
RoHS:	Yes
Lead:	Wire Leads

Specifications

Capacitance:	0.1 uF
Capacitance Tolerance:	10%
Voltage AC:	250 VAC
Voltage DC:	560 VDC, 336 VDC (105C)
Temperature Range:	-55/+105C
Rated Temperature:	85°C
Dissipation Factor:	0.04% 1kHz, 0.06% 10kHz, 0.25% 100kHz
Insulation Resistance:	100 GOhms
Max dV/dt:	500 V/us
Inductance:	10 nH