


FEATURES

- **Material:** Fluorinated Ethylene Propylene, Fluoroelastomer, Viton: Offers excellent chemical resistance and durability
- **Hardness:** Shore A 90 to 95: Ensures a firm and reliable seal
- **Temperature Range:** -20 °C to 140 °C: Suitable for a wide range of operating conditions
- **Inside Diameter:** 658.9 mm: Fits precisely for effective sealing
- **Outside Diameter:** 672.88 mm: Provides a secure fit in various applications
- **Thickness:** 6.99 mm: Ensures robust sealing capability

RS PRO 658.9 mm O-Ring Seal, Shore A 90 to 95

RS Stock No: 731-645



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO O-Ring Seal is designed for robust sealing applications, providing reliable performance in a variety of industrial environments. With a focus on durability and chemical resistance, this O-Ring is ideal for use in demanding conditions where high performance is essential.

General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

Mechanical Specifications

Inside Diameter	658.9 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	672.88 mm
Thickness	6.99 mm

Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

