




EAN:	4013288236265	Size:	225x50x30 mm
Part number:	05020363001	Weight:	126 g
Article number:	6007 Joker inch	Country of origin:	CZ
		Customs tariff number:	82041100

- Imperial sizes
- Brilliant combination of jaw end and ratchet mechanism at the ring end in a long design
- The long lever allows for higher power transmission and better accessibility at low-lying couplings
- Limit stop prevents any slipping
- With practical holding function by a metal plate in the mouth
- Return angle of only 30° in the open end
- The double-hex geometry reduces the risk of slipping
- With Take it easy tool finder: colour coding by size

Brilliant combination of jaw end and ratchet mechanism at the ring end in a long design. Imperial sizes. For hexagon screw heads and bolts. The long lever allows for higher power transmission. The long design also improves accessibility at low-lying couplings. With holding function enabled by a metal plate in the mouth, which reduces the risk of losing screws and sockets. With its extra hard teeth, the exchangeable metal plate in the mouth secures screws and sockets and reduces the risk of slipping. The integrated end stop can prevent the screw head from slipping down and allows application of high torque transfer. The double hexagon geometry ensures a positive connection with the screw or bolt and thus reduces the risk of slipping. A return angle of only 30° at the jaw end avoids time-consuming rotating of the tool whilst screwdriving. Ratchet mechanism at the ring side with exceptionally high fine tothing of 80 teeth for flexibility even in confined spaces. The specially engineered geometry allows high torque transmission and high bending stiffness. Made of high-performance chromium molybdenum steel with nickel-chromium coating for high corrosion protection. With Take it easy tool finder: colour coding by size and extra laser-engraved size indication.



Long design



Brilliant combination of jaw end and ratchet mechanism at the ring end in a long design. For hexagon screw heads and bolts. The long lever allows for higher power transmission. The long design also improves accessibility at low-lying couplings. With holding function enabled by a metal plate in the mouth, which reduces the risk of losing screws and sockets. With its extra hard teeth, the exchangeable metal plate in the mouth secures screws and sockets and reduces the risk of slipping. The integrated end stop can prevent the screw head from slipping down and allows application of high torque transfer. The double hexagon geometry ensures a positive connection with the screw or bolt and thus reduces the risk of slipping. A return angle of only 30° at the jaw end avoids time-consuming rotating of the tool whilst screwdriving. Ratchet mechanism at the ring side with exceptionally high fine toothing of 80 teeth for flexibility even in confined spaces. The specially engineered geometry allows high torque transmission and high bending stiffness. Made of high-performance chromium molybdenum steel with nickel-chromium coating for high corrosion protection. With Take it easy tool finder: colour coding by size and extra laser-engraved size indication.

With holding function for hexagonal screws and bolts




The Joker's holding function means that nuts and bolts can be held in the jaw and easily positioned where they are needed. Fastening on to the thread can then be done quickly and safely, thanks to the innovative special stop-plate which holds the fastener. No more time-wasting searches for dropped nuts and bolts! After applying and positioning the nut or bolt, fastening can begin immediately - no additional tools required.

Limit stop prevents any slipping



Thanks to its end stop, the Joker lowers the risk of the screw head slipping down. In addition, by reducing the risk of slipping, much more force can be applied when screwdriving.

Double-hex geometry



The Joker's clever double-hex geometry delivers a very positive connection with nuts or bolts - it's a perfect fit. Serrated teeth on the hardened metal plate provide grip in the Joker's open end literally bite themselves into the bolt, with its extremely hard tips. Both features combine to prevent slipping, even at higher torque.


Web link

<https://www.wera.de/en/05020363001>

Wera - 6007 Joker inch
05020363001 - 4013288236265

Wera Werkzeuge GmbH
Körzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Return angle of only 30° in the open end



The double hexagon geometry of the jaw end reduces the return angle of the Joker 6007 to 30°. The Joker 6007 has a straight jaw - awkward turning and repositioning is a thing of the past.

Fine tooth mechanism




The ratcheting feature at the ring end boasts an exceptional, fine tooth mechanism - 80 teeth in all - which provides greater flexibility, even in very confined workspaces.

Take it easy tool finder



Take it easy tool finder with colour coding by size and extra laser-engraved size indication - for quick and easy identification of the required tool.

Long design



The long design of the spanner improves accessibility at low-lying couplings.

Further versions in this product family:

							
		inch	mm	mm	mm	mm	mm
05020361001	blau_307C	5/16"	180	21	6	18	7
05020362001	rot_200C	3/8"	209	24.2	6.3	21	7.2
05020363001	violett_2735C	7/16"	220	26	7	23	7.5
05020364001	tuerkis_339C	1/2"	245	29.4	8	26	8.6
05020365001	pink_241C	9/16"	265	34	8.5	29	9.2
05020366001	schwarz_blackC	5/8"	304.5	39	9	33.5	10.5
05020367001	hellblau_5435C	11/16"	334	43	10	36	11
05020368001	gelb_123C	3/4"	334	43	10	36	11

Web link

<https://www.wera.de/en/05020363001>

Wera - 6007 Joker inch
05020363001 - 4013288236265

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de