

## Aluminum Capacitors Radial Low Leakage Current




Fig.1 Component outline.

**FEATURES**

- Polarized aluminum electrolytic capacitors, non-solid electrolyte
- Radial leads, cylindrical aluminum case, all-insulated (light blue)
- Natural pitch 2.5 mm and 5 mm
- Charge and discharge proof
- Miniaturized, high CV-product per unit volume
- Low leakage current, low energy consumption
- Lead (Pb)-Free versions are RoHS compliant


**RoHS  
COMPLIANT**
**APPLICATIONS**

- Telecommunication, automotive, audio-video, EDP and industrial
- Coupling, decoupling, buffering, timing, energy storage
- Portable and mobile equipment
- Low surface demand on printed-circuit board

**MARKING**


The capacitors are marked (where possible) with the following information:

- Rated capacitance (in  $\mu\text{F}$ )
- Tolerance on rated capacitance, code letter in accordance with IEC 60062 (M for  $\pm 20\%$ )
- Rated voltage (in V)
- Date code in accordance with IEC 60062
- Code indicating factory of origin
- Name of manufacturer
- Minus-sign on top to identify the negative terminal
- Series number (013)


QUICK REFERENCE DATA	
DESCRIPTION	VALUE
Nominal case sizes ( $\varnothing$ D x L in mm)	5 x 11 and 8.2 x 11
Rated capacitance range, $C_R$	0.47 to 470 $\mu\text{F}$
Tolerance on $C_R$	$\pm 20\%$ ; $\pm 10\%$ on request
Rated voltage range, $U_R$	6.3 to 50 V
Category temperature range	- 40 to + 85 °C
Leakage current after 2 minutes: $U_R = 6.3$ to 25 V	0.002 $C_R \times U_R$ or 0.7 $\mu\text{A}$ , whichever is greater
$U_R = 35$ and 50 V	0.002 $C_R \times U_R + 1 \mu\text{A}$
Endurance test at 85 °C	2000 hours
Useful life at 105 °C	750 hours
Useful life at 85 °C	3000 hours
Useful life at 40 °C, 1.4 x $I_R$ applied	80 000 hours
Shelf life at 0 V, 85 °C	500 hours
Based on sectional specification	IEC 60384-4/EN130300
Climatic category IEC 60068	40/085/56

SELECTION CHART FOR $C_R$ , $U_R$ AND RELEVANT NOMINAL CASE SIZES ( $\varnothing$ D x L in mm)						
$C_R$ ( $\mu\text{F}$ )	$U_R$ (V)					
	6.3	10	16	25	35	50
0.47	-	-	-	-	-	5 x 11
1.0	-	-	-	5 x 11	-	5 x 11
2.2	-	-	-	5 x 11	-	5 x 11
3.3	-	-	-	5 x 11	-	5 x 11
4.7	-	-	-	5 x 11	-	5 x 11
10	-	-	-	5 x 11	-	5 x 11
22	-	-	-	5 x 11	-	5 x 11
33	-	-	5 x 11	-	5 x 11	8.2 x 11
47	-	5 x 11	5 x 11	8.2 x 11	-	8.2 x 11
68	-	5 x 11	-	-	-	8.2 x 11
100	-	5 x 11	-	-	8.2 x 11	-
220	-	8.2 x 11	-	-	-	-
330	8.2 x 11	-	-	-	-	-
470	8.2 x 11	-	-	-	-	-


**DIMENSIONS** in millimeters **AND AVAILABLE FORMS**



**Fig.2 Form CA: Long leads**




**Fig.3 Form CB: Cut leads**



Case  $\varnothing D \times L = 5 \times 11$  and  $8.2 \times 11$  mm  
Pitch  $F = 5$  mm

**Fig.4 Form TFA: Taped in box (ammopack)**



Case  $\varnothing D \times L = 5 \times 11$  mm only  
Pitch  $F = 2.5$  mm

**Fig.5 Form TFA: Taped in box (ammopack)**

<b>DIMENSIONS</b> in millimeters, <b>MASS AND PACKAGING QUANTITIES</b>								
NOMINAL CASE SIZE $\varnothing D \times L$	CASE CODE	$\varnothing d$	$\varnothing D_{max}$	$L_{max}$	F	MASS (g)	PACKAGING QUANTITIES	
							FORM CA, CB	FORM TFA, TNA
5 x 11	11	0.5	5.5	12	$2.5 \pm 0.5$	$\approx 0.4$	1000	2000
8.2 x 11	13	0.6	8.7	12	$5.0 \pm 0.5$	$\approx 1.1$	1000	1000

**Note**

Detailed tape dimensions see section 'PACKAGING'.



Aluminum Capacitors  
Radial Low Leakage Current

Vishay BCcomponents

ELECTRICAL DATA	
SYMBOL	DESCRIPTION
C <sub>R</sub>	rated capacitance at 100 Hz, tolerance ± 20 %
I <sub>R</sub>	rated RMS ripple current at 100 Hz, 85 °C
I <sub>L2</sub>	max. leakage current after 2 minutes at U <sub>R</sub>
Tan δ	max. dissipation factor at 100 Hz
Z	max. impedance at 10 kHz and + 20 °C

**ORDERING EXAMPLE**

Electrolytic capacitor 013 series  
 100 µF/16 V; ± 20 %  
 Nominal case size: Ø 8.2 x 11 mm; Form TFA  
 Ordering Code: MAL201335101E3  
 Former 12NC: 2222 013 35101

**Note**

- Unless otherwise specified, all electrical values in Table 1 apply at T<sub>amb</sub> = 20 °C, P = 86 to 106 kPa, RH = 45 to 75 %.


Table 1

ELECTRICAL DATA AND ORDERING INFORMATION																
U <sub>R</sub> (V)	C <sub>R</sub> 100 Hz (µF)	NOMINAL CASE SIZE Ø D × L (mm)	I <sub>R</sub> 100 Hz 85 °C (mA)	I <sub>L2</sub> 2 min (µA)	TAN Δ 100 Hz	Z 10 kHz (Ω)	CATALOG NUMBER 2222 013 .....									
							BULK PACKAGING				TAPED AMMOPACK					
							LONG LEADS		CUT LEADS		FORM TFA		FORM TNA		FORM F	
							FORM CA	F (mm)	FORM CB	F (mm)	FORM TFA	F (mm)	FORM TNA	F (mm)		
6.3	330	8.2 x 11	210	4.2	0.2	0.9	53331E3	5.0	63331E3	5.0	33331E3	5.0	-	-		
	470	8.2 x 11	250	5.9	0.2	0.64	53471E3	5.0	63471E3	5.0	33471E3	5.0	-	-		
10	47	5 x 11	75	1.0	0.16	2.8	54479E3	2.5	-	-	34479E3	5.0	74479E3	2.5		
	68	5 x 11	90	1.4	0.16	2.5	54689E3	2.5	-	-	34689E3	5.0	74689E3	2.5		
	100	5 x 11	110	2.0	0.16	1.7	54101E3	2.5	-	-	34101E3	5.0	74101E3	2.5		
	220	8.2 x 11	190	4.4	0.16	0.9	54221E3	5.0	64221E3	5.0	34221E3	5.0	-	-		
16	33	5 x 11	70	1.1	0.13	2.8	55339E3	2.5	-	-	35339E3	5.0	75339E3	2.5		
	47	5 x 11	85	1.5	0.13	2.1	55479E3	2.5	-	-	35479E3	5.0	75479E3	2.5		
	100	8.2 x 11	150	3.2	0.13	1.0	55101E3	5.0	65101E3	5.0	35101E3	5.0	-	-		
25	1.0	5 x 11	5	0.7	0.06	40	56108E3	2.5	-	-	36108E3	5.0	76108E3	2.5		
	2.2	5 x 11	10	0.7	0.06	18	56228E3	2.5	-	-	36228E3	5.0	76228E3	2.5		
	3.3	5 x 11	18	0.7	0.06	12	56338E3	2.5	-	-	36338E3	5.0	76338E3	2.5		
	4.7	5 x 11	25	0.7	0.06	8.5	56478E3	2.5	-	-	36478E3	5.0	76478E3	2.5		
	10	5 x 11	50	0.7	0.06	4.0	56109E3	2.5	-	-	36109E3	5.0	76109E3	2.5		
	22	5 x 11	75	1.1	0.08	2.7	56229E3	2.5	-	-	36229E3	5.0	76229E3	2.5		
	47	8.2 x 11	130	2.4	0.08	1.3	56479E3	5.0	66479E3	5.0	36479E3	5.0	-	-		
35	33	5 x 11	70	3.3	0.13	2.8	50339E3	5.0	-	-	30339E3	5.0	70339E3	2.5		
	100	8.2 x 11	150	8.0	0.13	1.0	50101E3	5.0	60101E3	5.0	30101E3	5.0	-	-		
50	0.47	5 x 11	5	1.1	0.06	85	51477E3	2.5	-	-	31477E3	5.0	71477E3	2.5		
	1.0	5 x 11	10	1.1	0.06	40	51108E3	2.5	-	-	31108E3	5.0	71108E3	2.5		
	2.2	5 x 11	20	1.2	0.06	18	51228E3	2.5	-	-	31228E3	5.0	71228E3	2.5		
	3.3	5 x 11	32	1.3	0.06	12	51338E3	2.5	-	-	31338E3	5.0	71338E3	2.5		
	4.7	5 x 11	38	1.5	0.06	8.5	51478E3	2.5	-	-	31478E3	5.0	71478E3	2.5		
	10	5 x 11	55	2.0	0.06	4.0	51109E3	2.5	-	-	31109E3	5.0	71109E3	2.5		
	22	5 x 11	75	3.2	0.08	2.7	51229E3	2.5	-	-	31229E3	5.0	71229E3	2.5		
	33	8.2 x 11	110	4.3	0.06	1.4	51339E3	5.0	61339E3	5.0	31339E3	5.0	-	-		
	47	8.2 x 11	130	5.7	0.08	1.3	51479E3	5.0	61479E3	5.0	31479E3	5.0	-	-		
68	8.2 x 11	150	7.8	0.08	1.2	51689E3	5.0	61689E3	5.0	31689E3	5.0	-	-			




ADDITIONAL ELECTRICAL DATA		
PARAMETER	CONDITIONS	VALUE
<b>Voltage</b>		
Surge voltage		$U_s \leq 1.3 \times U_R$
Reverse voltage		$U_{rev} \leq 1 \text{ V}$
<b>Current</b>		
Leakage current	after 2 minutes at $U_R$ : $U_R = 6.3 \text{ to } 25 \text{ V}$ $U_R = 35 \text{ and } 50 \text{ V}$	$I_{L2} \leq 0.002 C_R \times U_R$ or $0.7 \mu\text{A}$ , whichever is greater $I_{L2} \leq 0.002 C_R \times U_R + 1 \mu\text{A}$
<b>Inductance</b>		
Equivalent series inductance (ESL)	case $\varnothing D \times L = 5 \times 11 \text{ mm}$	typ. 13 nH
	case $\varnothing D \times L = 8.2 \times 11 \text{ mm}$	typ. 16 nH
<b>Resistance</b>		
Equivalent series resistance (ESR)	calculated from $\tan \delta_{max}$ and $C_R$ (see Table 1)	$ESR = \tan \delta / 2\pi f C_R$

**CAPACITANCE (C)**




**Fig.6** Typical multiplier of capacitance as a function of ambient temperature




**Fig.7** Typical multiplier of capacitance as a function of frequency

**LEAKAGE CURRENT**




**Fig.8** Typical multiplier of leakage current as a function of ambient temperature




**Fig.9** Typical multiplier of leakage current as a function of time

**LEAKAGE CURRENT**



**Fig.10** Typical multiplier of leakage current a function of time

**RIPPLE CURRENT AND USEFUL LIFE**



$I_A$  = Actual ripple current at 100 Hz  
 $I_R$  = Ripple current at 85 °C, 100 Hz  
 (1) Useful life at 85 °C and  $I_R$  ripple current load

**Fig.11** Multiplier of useful life as a function of ambient temperature and ripple current load

**Table 2**

<b>MULTIPLIER OF RIPPLE CURRENT (<math>I_R</math>) AS A FUNCTION OF FREQUENCY</b>			
<b>FREQUENCY (Hz)</b>	<b><math>I_R</math> MULTIPLIER</b>		
	<b><math>U_R = 6.3 V</math></b>	<b><math>U_R = 10, 16 \text{ and } 35 V</math></b>	<b><math>U_R = 25 \text{ and } 50 V</math></b>
50	0.90	0.85	0.80
100	1.00	1.00	1.00
300	1.12	1.20	1.25
1000	1.20	1.30	1.40
3000	1.25	1.35	1.50
$\geq 10\ 000$	1.30	1.40	1.60

Table 3

<b>TEST PROCEDURES AND REQUIREMENTS</b>			
<b>TEST</b>		<b>PROCEDURE</b>	<b>REQUIREMENTS</b>
<b>NAME OF TEST</b>	<b>REFERENCE</b>		
Endurance	IEC 60384-4/ EN130300, subclause 4.13	$T_{amb} = 85\text{ }^{\circ}\text{C}$ ; $U_R$ applied; 2000 hours	$U_R \leq 6.3\text{ V}$ ; $\Delta C/C$ : + 15/- 30 % $U_R > 6.3\text{ V}$ ; $\Delta C/C$ : $\pm 15\%$ $\tan \delta \leq 1.3 \times \text{spec. limit}$ $Z \leq 2 \times \text{spec. limit}$ $I_{L2} \leq \text{spec. limit}$
Useful life	CECC 30301, subclause 1.8.1	$T_{amb} = 85\text{ }^{\circ}\text{C}$ ; $U_R$ and $I_R$ applied; 3000 hours	$U_R \leq 6.3\text{ V}$ ; $\Delta C/C$ : + 45/- 50 % $U_R > 6.3\text{ V}$ ; $\Delta C/C$ : $\pm 45\%$ $\tan \delta \leq 3 \times \text{spec. limit}$ $Z \leq 3 \times \text{spec. limit}$ $I_{L2} \leq \text{spec. limit}$ no short or open circuit total failure percentage: $\leq 1\%$
Shelf life (storage at high temperature)	IEC 60384-4/ EN130300, subclause 4.17	$T_{amb} = 85\text{ }^{\circ}\text{C}$ ; no voltage applied; 500 hours after test: $U_R$ to be applied for 30 minutes, 24 to 48 hours before measurement	$\Delta C/C$ , $\tan \delta$ , $Z$ : for requirements see 'Endurance test' above $I_{L2} \leq 2 \times \text{spec. limit}$



## Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.