

# BUMPER

## Oval Buffer Extended 65L x 39W x 52H

SKU.: 0734068


### Features

- **Forklift Safety** – Reduce collision damage in warehouses and industrial areas
- **Loading Bays**– Cushion impacts to protect goods and infrastructure
- **Vibration Damping** – Minimizes noise and mechanical vibrations



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

# BUMPER



## Bumper Dimensions

Length (mm)	65
Width (mm)	39
Height (mm)	52

# BUMPER

## Product Description

Oval Rubber Bumper Stops are a vital safety accessory crafted from heavy-duty SBR rubber, engineered to withstand repeated impacts, resist wear, and endure harsh environmental conditions, ensuring long-lasting protection for vehicles, equipment, and property. Their versatile design allows quick and secure installation on a wide range of surfaces, making them suitable for industrial, commercial, and residential use. These bumper stops provide reliable cushioning to safeguard cars, trailers, and lorries during loading and unloading, enhance workplace safety by reducing collision risks with forklift trucks, offer added support for glass rack carriers in transit, and protect loading bays from damage when handling goods. Beyond industrial applications, they also serve as effective door and furniture buffers, preventing everyday wear and tear in homes and offices. By combining durability, functionality, and adaptability, Oval Rubber Bumper Stops deliver a comprehensive solution for impact protection across diverse environments, helping extend the life of valuable assets while maintaining safety and efficiency.

## General Specifications

<b>Material</b>	NR/SBR
<b>Colour</b>	Black

## Mechanical Specifications

<b>Weight</b>	0.09KG
<b>Tensile Strength</b>	4Mpa
<b>Elongation</b>	200%
<b>Hardness</b>	75ShA

## Operation Environment Specifications

<b>Maximum Temperature</b>	70°C
<b>Minimum Temperature</b>	-15°C