



Figure similar

SIMATIC ET 200SP Open Controller, CPU 1515SP PC2 F, 8 GB RAM (basic device 6ES7677-2DB40-0AA0), 128 GB CFast with Windows 10 IoT Enterprise LTSC 2021 64-bit and S7-1500 Failsafe Software Controller CPU 1505SP F V3x preinstalled; interfaces: 1x slot CFast, 1x slot SD/MMC, 1x connection for ET 200SP BusAdapter PROFINET, 1x 10/100/1000 Mbps Ethernet, 2x USB 3.0, 2x USB 2.0, 1x DisplayPort; documentation on CFast, restore image on CFast

General information	
Product type designation	CPU 1515SP PC2 F
Firmware version	V30.1
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M3
<ul style="list-style-type: none"> Isochronous mode 	Yes; only with PROFINET; with minimum OB 6x cycle of 500 µs
<ul style="list-style-type: none"> SysLog 	Yes
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated from version 	V19
Installed software	
<ul style="list-style-type: none"> Visualization 	No
<ul style="list-style-type: none"> Control 	S7-1500 Software Controller CPU 1505SP F
Configuration control	
via dataset	Yes
Control elements	
Mode selector switch	1
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Mains buffering	
<ul style="list-style-type: none"> Mains/voltage failure stored energy time 	5 ms
Input current	
Current consumption (rated value)	1.8 A; Full processor load, incl. ET 200SP modules and using USB
Current consumption (in no-load operation), typ.	0.5 A
Current consumption, max.	2.9 A
I ² t	0.426 A ² -s; with starting current inrush
Power	
Active power input, max.	43 W; incl. ET 200SP modules and using USB
Infeed power to the backplane bus	8.75 W
Power loss	
Power loss, typ.	16 W
Processor	
Processor type	Intel Atom E3940, 1.6 GHz, 4 cores
Memory	
Type of memory	DDR3L
Main memory	8 GB RAM

CFast memory card	Yes; 128 GB flash memory
SIMATIC memory card required	No
Work memory	
• integrated (for program)	3 Mbyte
• integrated (for data)	7.5 Mbyte
• integrated (for CPU function library of CPU Runtime)	20 Mbyte
Load memory	
• integrated (on PC mass storage)	320 Mbyte
Backup	
• with UPS	Yes; all memory areas declared retentive
• with non-volatile memory	Yes
CPU-blocks	
Number of elements (total)	8 000; In addition to blocks such as DBs, FBs and FCs, UDTs, global constants, etc. are also regarded as elements
DB	
• Number, max.	7 999; Number range: 1 to 65535
• Size, max.	5 Mbyte
FB	
• Number, max.	7 998; Number range: 1 to 65535
• Size, max.	1 024 kbyte
FC	
• Number, max.	7 999; Number range: 1 to 65535
• Size, max.	1 024 kbyte
OB	
• Size, max.	1 024 kbyte
• Number of free cycle OBs	100
• Number of time alarm OBs	20
• Number of delay alarm OBs	20
• Number of cyclic interrupt OBs	20
• Number of process alarm OBs	50
• Number of DPV1 alarm OBs	3
• Number of isochronous mode OBs	1
• Number of technology synchronous alarm OBs	2
• Number of startup OBs	100
• Number of asynchronous error OBs	4
• Number of synchronous error OBs	2
• Number of diagnostic alarm OBs	1
Nesting depth	
• per priority class	24; Up to 8 possible for F-blocks
Counters, timers and their retentivity	
S7 counter	
• Number	2 048
Retentivity	
— adjustable	Yes
IEC counter	
• Number	Any (only limited by the main memory)
Retentivity	
— adjustable	Yes
S7 times	
• Number	2 048
Retentivity	
— adjustable	Yes
IEC timer	
• Number	Any (only limited by the main memory)
Retentivity	
— adjustable	Yes
Data areas and their retentivity	
Retentive data area (incl. timers, counters, flags), max.	410 kbyte; For storage in NVRAM; for storage in mass storage 5 242 020 bytes
Flag	

• Size, max.	16 kbyte
• Number of clock memories	8; 8 clock memory bit, grouped into one clock memory byte
Data blocks	
• Retentivity adjustable	Yes
• Retentivity preset	No
Local data	
• per priority class, max.	64 kbyte; max. 16 KB per block
Address area	
Number of IO modules	8 192
I/O address area	
• Inputs	32 kbyte; All inputs are in the process image
• Outputs	32 kbyte; All outputs are in the process image
Subprocess images	
• Number of subprocess images, max.	32
Hardware configuration	
Integrated power supply	Yes
Number of distributed IO systems	20
Number of DP masters	
• Via CM	1
Number of IO Controllers	
• via PC interfaces	1
Rack	
• Modules per rack, max.	82; CPU + 64 modules + server module (mounting width max. 1 m) + 16 ET 200AL modules
• Quantity of operable ET 200SP modules, max.	64
• Quantity of operable ET 200AL modules, max.	16
• Number of lines, max.	1
PtP CM	
• Number of PtP CMs	the number of connectable PtP CMs is only limited by the number of available slots
Time of day	
Clock	
• Type	Hardware clock
• Hardware clock (real-time)	Yes; Resolution: 1 s
• Backup time	6 wk; At 40 °C ambient temperature, typically
• Deviation per day, max.	10 s; Typ.: 2 s
Clock synchronization	
• supported	Yes
• to DP, master	Yes; Via CM DP module
• on Ethernet via NTP	Yes
• on Windows clock, device	Yes
Interfaces	
Number of industrial Ethernet interfaces	2
Number of PROFINET interfaces	1
Number of PROFIBUS interfaces	1; Via CM DP module
Number of RS 485 interfaces	1; Via CM DP module
Number of USB interfaces	4; 2x USB 2.0, 2x USB 3.0 on front side
Number of SD card slots	1
Video interfaces	
• Graphics interface	1x DisplayPort
1. Interface	
Interface type	PROFINET
automatic detection of transmission rate	Yes
Autonegotiation	Yes
Autocrossing	Yes
Number of connections	88
Interface types	
• RJ 45 (Ethernet)	Yes; Via BusAdapter BA 2x RJ45
— Transmission rate, max.	100 Mbit/s

— Industrial Ethernet status LED	Yes
● Number of ports	2
● integrated switch	Yes
● BusAdapter (PROFINET)	Yes; compatible BusAdapters: BA 2x RJ45, BA 2x M12, BA 2x FC, BA 2x LC, BA LC/RJ45, BA LC/FC, BA 2x SCRJ, BA SCRJ/RJ45, BA SCRJ/FC
Protocols	
● IP protocol	Yes; IPv4
● PROFINET IO Controller	Yes
● PROFINET IO Device	Yes
● SIMATIC communication	Yes
● Open IE communication	Yes; Optionally also encrypted
● Web server	Yes
● Media redundancy	Yes
PROFINET IO Controller	
Services	
— Isochronous mode	Yes
— Direct data exchange	Yes; Requirement: IRT and isochronous mode (MRPD optional)
— shortest clock pulse	500 µs
— IRT	Yes
— PROFIenergy	Yes
— Prioritized startup	Yes; Max. 32 PROFINET devices
— Number of connectable IO Devices, max.	128
— Of which IO devices with IRT, max.	64
— of which in line, max.	64
— Number of connectable IO Devices for RT, max.	128
— of which in line, max.	128
— Number of IO Devices that can be simultaneously activated/deactivated, max.	8
— IO Devices changing during operation (partner ports), supported	Yes
— Number of IO Devices per tool, max.	8
— Updating times	The minimum value of the update time also depends on communication share set for PROFINET IO, on the number of IO devices, and on the quantity of configured user data
— PROFINET Security Class	1
Update time for IRT	
— for send cycle of 500 µs	500 µs to 8 ms
— for send cycle of 1 ms	1 ms to 16 ms
— for send cycle of 2 ms	2 ms to 32 ms
— for send cycle of 4 ms	4 ms to 64 ms
— With IRT and parameterization of "odd" send cycles	Update time = set "odd" send clock (any multiple of 125 µs: 625 µs ... 3 875 µs) minimum cycle time start from 500 µs
Update time for RT	
— for send cycle of 500 µs	500 µs to 256 ms
— for send cycle of 1 ms	1 ms to 512 ms
— for send cycle of 2 ms	2 ms to 512 ms
— for send cycle of 4 ms	4 ms to 512 ms
Address area	
— Inputs, max.	8 kbyte
— Outputs, max.	8 kbyte
PROFINET IO Device	
Services	
— Isochronous mode	No
— IRT	Yes
— PROFIenergy	Yes; per user program
— Prioritized startup	Yes
— Shared device	Yes
— Number of IO Controllers with shared device, max.	4
— activation/deactivation of I-devices	Yes; per user program
— Asset management record	Yes; per user program
— PROFINET Security Class	SNMP Configuration and DCP Read Only

2. Interface	
Interface type	Integrated Ethernet interface
automatic detection of transmission rate	Yes
Autonegotiation	Yes
Autocrossing	Yes
Interface types	
<ul style="list-style-type: none"> ● RJ 45 (Ethernet) <ul style="list-style-type: none"> — Transmission rate, max. — Industrial Ethernet status LED ● Number of ports 	Yes; Integrated 1 000 Mbit/s No 1
3. Interface	
Interface type	PROFIBUS with CM DP
Number of connections	44
Interface types	
<ul style="list-style-type: none"> ● RS 485 	Yes
Protocols	
<ul style="list-style-type: none"> ● PROFIBUS DP master ● PROFIBUS DP device ● SIMATIC communication 	Yes Yes Yes
PROFIBUS DP master	
<ul style="list-style-type: none"> ● max. number of DP devices 	125
Services	
<ul style="list-style-type: none"> — Equidistance — Isochronous mode 	No No
Address area	
<ul style="list-style-type: none"> — Inputs, max. — Outputs, max. 	8 kbyte 8 kbyte
Interface types	
RS 485	
<ul style="list-style-type: none"> ● Transmission rate, max. 	12 Mbit/s
Protocols	
PROFIsafe	Yes
Number of connections	
<ul style="list-style-type: none"> ● Number of connections, max. ● Number of connections reserved for ES/HMI/web ● Number of S7 routing paths 	88 10 16
Redundancy mode	
Media redundancy	
<ul style="list-style-type: none"> — Media redundancy — MRP — MRP interconnection, supported — MRPD — Switchover time on line break, typ. — Number of stations in the ring, max. 	Yes; only via BusAdapter Yes; MRP Automanager according to IEC 62439-2 Edition 2.0, MRP Manager; MRP Client Yes; as MRP ring node according to IEC 62439-2 Edition 3.0 Yes; Requirement: IRT 200 ms; For MRP, bumpless for MRPD 50
SIMATIC communication	
<ul style="list-style-type: none"> ● PG/OP communication ● S7 routing ● S7 communication, as server ● S7 communication, as client ● User data per job, max. 	Yes; encryption with TLS V1.3 pre-selected Yes Yes Yes 64 kbyte; BSEND/BRCV: 64 KB; PUT/GET: 960 bytes
Open IE communication	
<ul style="list-style-type: none"> ● TCP/IP <ul style="list-style-type: none"> — Data length, max. ● ISO-on-TCP (RFC1006) <ul style="list-style-type: none"> — Data length, max. ● UDP <ul style="list-style-type: none"> — Data length, max. — UDP multicast 	Yes 64 kbyte Yes 64 kbyte Yes 2 kbyte; 1 472 bytes for UDP broadcast Yes; Max. 5 multicast circuits

• DHCP	Yes
• DNS	Yes
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
• Encryption	Yes; Optional
Web server	
• HTTP	Yes; Standard and user pages
• HTTPS	Yes; Standard and user pages
• web API	
— Number of sessions, max.	50
— number of simultaneous HTTP calls, max.	4
— HTTP request body, max.	131 072 byte
OPC UA	
• Runtime license required	Yes; "Small" license required
• OPC UA Client	Yes; Data access (read, write), method call
— Application authentication	Yes
— Security policies	Yes; Available security policies: None, Basic128Rsa15, Basic256Rsa15, Basic256Sha256
— User authentication	Yes; "anonymous" or by user name & password
— Number of connections, max.	10
— Number of nodes of the client interfaces, recommended max.	2 000
— Number of elements for one call of OPC-UA-NodeGetHandleList/OPC-UA-ReadList/OPC-UA-WriteList, max.	300
— Number of elements for one call of OPC-UA-NameSpaceGetIndexList, max.	20
— Number of elements for one call of OPC-UA-MethodGetHandleList, max.	100
— Number of simultaneous calls of the client instructions for session management, per connection, max.	1
— Number of simultaneous calls of the client instructions for data access, per connection, max.	5
— Number of registerable nodes, max.	5 000
— Number of registerable method calls of OPC-UA-MethodCall, max.	100
— Number of inputs/outputs when calling OPC-UA-MethodCall, max.	20
• OPC UA Server	Yes; Data access (read, write, subscribe), method call, custom address space
— Application authentication	Yes
— Security policies	Yes; Available security policies: None, Basic128Rsa15, Basic256Rsa15, Basic256Sha256
— User authentication	Yes
— GDS support (certificate management)	Yes
— Number of sessions, max.	48
— Number of accessible variables, max.	100 000
— Number of registerable nodes, max.	20 000
— Number of subscriptions per session, max.	50
— Sampling interval, min.	100 ms
— Publishing interval, min.	200 ms
— Number of server methods, max.	50
— Number of inputs/outputs per server method, max.	20
— Number of monitored items, recommended max.	2 000; for 1 s sampling interval and 1 s send interval
— Number of server interfaces, max.	10
— Number of nodes for user-defined server interfaces, max.	5 000
• Alarms and Conditions	Yes
— Number of program alarms	200
— Number of alarms for system diagnostics	100
Further protocols	
• MODBUS	Yes; MODBUS TCP

S7 message functions

Number of login stations for message functions, max.	32
Program alarms	Yes
Number of configurable program messages, max.	10 000
Number of simultaneously active program alarms	1 000
• Number of program alarms	1 000
• Number of alarms for system diagnostics	200
• Number of alarms for motion technology objects	160

Test commissioning functions

Joint commission (Team Engineering)	Yes; Parallel online access possible for up to 10 engineering systems
Status block	Yes; up to 8 simultaneously
Single step	Yes
Number of breakpoints	8
Profiling	No

Status/control

• Status/control variable	Yes
• Variables	Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters
• Number of variables, max.	
— of which status variables, max.	200; per job
— of which control variables, max.	200; per job

Forcing

• Forcing	Yes
• Forcing, variables	Peripheral inputs/outputs
• Number of variables, max.	200

Diagnostic buffer

• present	Yes
• Number of entries, max.	1 000
— of which powerfail-proof	300

Traces

• Number of configurable Traces	4
• Memory size per trace, max.	512 kbyte

Interrupts/diagnostics/status information**Diagnostics indication LED**

• RUN/STOP LED	Yes
• ERROR LED	Yes
• MAINT LED	Yes

Supported technology objects

Motion Control	Yes; Note: The number of technology objects affects the cycle time of the PLC program; selection guide via the TIA Selection Tool or SIZER
• Number of available Motion Control resources for technology objects	2 400
• Required Motion Control resources	
— per speed-controlled axis	40
— per positioning axis	80
— per synchronous axis	160
— per external encoder	80
— per output cam	20
— per cam track	160
— per probe	40
• Positioning axis	
— Number of positioning axes at motion control cycle of 4 ms (typical value)	30
— Number of positioning axes at motion control cycle of 8 ms (typical value)	30
Controller	
• PID_Compact	Yes; Universal PID controller with integrated optimization
• PID_3Step	Yes; PID controller with integrated optimization for valves
• PID-Temp	Yes; PID controller with integrated optimization for temperature
Counting and measuring	
• High-speed counter	Yes

Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
Highest safety class achievable in safety mode	
<ul style="list-style-type: none"> • Performance level according to ISO 13849-1 • SIL acc. to IEC 61508 	PLe SIL 3
Probability of failure (for service life of 20 years and repair time of 100 hours)	
— Low demand mode: PFDavg in accordance with SIL3	< 2.00E-05
— High demand/continuous mode: PFH in accordance with SIL3	< 1.00E-09 1/h
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> • min. • horizontal installation, min. • horizontal installation, max. • vertical installation, min. • vertical installation, max. 	-20 °C -20 °C 60 °C; from 55°C: with max. 32 ET 200SP modules; 4x 0.3 A USB load; CFast memory card max. 10% load; SD card not used -20 °C 50 °C; from 45°C: with max. 32 ET 200SP modules; 4x 0.3 A USB load; CFast memory card and SD card; max. 10% load
Ambient temperature during storage/transportation	
<ul style="list-style-type: none"> • min. • max. 	-40 °C 70 °C
Vibrations	
<ul style="list-style-type: none"> • Operation, tested according to IEC 60068-2-6 • Transport, tested acc. to IEC 60068-2-6 	Yes Yes
Shock testing	
<ul style="list-style-type: none"> • tested according to IEC 60068-2-6 • tested according to IEC 60068-2-27 • tested according to IEC 60068-2-29 • Storage/transport, tested acc. to IEC 60068-2-27 	Yes Yes Yes Yes
Operating systems	
pre-installed operating system	Windows 10 IoT Enterprise 2021 LTSC
Configuration	
Programming	
Programming language	
— LAD	Yes; incl. failsafe
— FBD	Yes; incl. failsafe
— STL	Yes
— SCL	Yes
— CFC	No
— GRAPH	Yes
Know-how protection	
<ul style="list-style-type: none"> • User program protection/password protection • Copy protection • Block protection 	Yes Yes Yes
Access protection	
<ul style="list-style-type: none"> • protection of confidential configuration data • Protection level: Write protection • Protection level: Read/write protection • Protection level: Write protection for Failsafe • Protection level: Complete protection • User administration • Number of users 	Yes Yes Yes Yes Yes Yes; device-wide 100
Cycle time monitoring	
<ul style="list-style-type: none"> • lower limit • upper limit 	adjustable minimum cycle time adjustable maximum cycle time

Open Development interfaces	
• Size of ODK SO file, max.	5.8 Mbyte
Peripherals/Options	
SD card	Optionally for additional mass storage
Dimensions	
Width	160 mm
Height	117 mm
Depth	75 mm
Weights	
Weight, approx.	0.83 kg
Classifications	

	Version	Classification
eClass	14	27-24-26-07
eClass	12	27-24-26-07
eClass	9.1	27-24-26-07
eClass	9	27-24-26-07
eClass	8	27-24-26-07
eClass	7.1	27-24-26-07
eClass	6	27-24-26-07
ETIM	10	EC001603
ETIM	9	EC001603
ETIM	8	EC001603
ETIM	7	EC001603
IDEA	4	3565
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)

[Miscellaneous](#)

[China RoHS](#)

[Miscellaneous](#)



[TUEV](#)

Maritime application



last modified:

7/17/2025