


6.2



NOTES:

1. Rating: Input : 100~240VAC
Output : 3~30VDC 10A
2. Insulation Withstands Voltage:
AC 2500V at 1 minute
3. Insulation Resistance:
500M.Ω or more at DC500V
4. Operation Temperature Range:
-25°C~+60°C
5. Screw Torque Value: 0.4N.m
6. Suitable Electric Wire: AWG 24~12
7. RoHS Compliance

Normal Geometric Tolerancing				
—	//	≡	⊥	
0 to 100	0.2	0.3	0 to 10	0.2
over 100 to 150	0.3		over 10	0.3
over 150	0.5			
Total Pitch Tolerances		Normal Dimension Tolerances		
0~30	±0.20	0~30	±0.25	
over 30~53	±0.25	over 30~53	±0.30	
over 53~70	±0.30	over 53~70	±0.35	
over 70~90	±0.35	over 70~90	±0.44	
over 90~115	±0.44	over 90~115	±0.55	
over 115~150	±0.55	over 115~150	±0.70	
over 150~200	±0.70	over 150~200	±0.85	
over 200~250	±0.85	over 200~250	±1.00	
over 250~320	±1.00	over 250~320	±1.20	

3	JUMPER		GRAY
2	RE-1213-W		BLACK
1	COVER	PA66	BLACK
ITEM	NAME OF PART	MATERIAL	NOTES

DWG.	W.ZJ	DATE	15.02.11	UNITS	MM	SHEET/OF	1 / 1
CHK.		DATE		SCALE	1.5:1 (:)		
APP.		DATE		NAME	RE-1213		
				DWG NO.	SP-03-RE121300		

	REV.	CONTENT	NAME	DATE