



TE Internal #: 324693
Closed End Splice, Copper, 13.08 mm [.515 in] Length, Loose
Piece, Closed Barrel, Solid / Stranded Wire, Copper Wire, Discrete
Wire, Fully Insulated
[View on TE.com >](#)

Terminals & Splices > Splices



Splice Type: **Closed End Splice**
Sealable: **No**
Contact Base Material: **Copper**
Terminal Material Thickness: **.51 mm [.02 in]**
Product Length: **13.08 mm [.515 in]**

Features

Product Type Features

Splice Accessory Type	Wire Cap
Splice Type	Closed End Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Insulation Material	Nylon
---------------------	-------

Contact Features

Contact Base Material	Copper
Barrel Type	Closed

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------



Dimensions

Outside Diameter	3.61 mm[.142 in]
Terminal Material Thickness	.51 mm[.02 in]
Product Length	13.08 mm[.515 in]

Usage Conditions

Insulation Option	Fully Insulated
-------------------	-----------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58573-1
SPARE WIRE CAPPER ASSEMBLY

TE Part # 58573-2
PROCrimp DIE SPARE WIRE CAP

Customers Also Bought

TE Part #1445693-3
SOCKET CONTACT,QUADRIX,SZ8,RR

TE Part #CTM-20
BORNE JONCTION

TE Part #ABC03N-22P-4048
IN-LINE RECP

TE Part #324484
SPARE WIRE CAP,NAT .048-.075 INS.

TE Part #D369-P99-NS1
369 9 WAY PLUG, CRIMP, SKT

TE Part #D369-P33-NS1
369 3 WAY PLUG, CRIMP, SKT

TE Part #D369-R99-NP1
369 9 WAY REC, CRIMP, PIN

TE Part #YCTJ122E02DC015000
ELEC MODULE

TE Part #D369-R66-NP1
369 6 WAY REC, CRIMP, PIN

TE Part #YD369-R33-NP300000
369 3 WAY REC, CRIMP, PIN, 20/22

Documents

Product Drawings
SPARE WIRE CAP,NAT, .048-.075 INS., MOIS
English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_324693_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_324693_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_324693_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English