



CE S 48 018 -30 -□

① ② ③ ④ ⑤ ⑥



- ① Series name
 ② Single output
 ③ Input voltage
 24 : DC18 - 36V
 48 : DC36 - 76V
 ④ Output voltage
 015:1.5V
 018:1.8V
 025:2.5V
 033:3.3V
 050:5V
 060:6V
 120:12V
 150:15V
 ⑤ Output current
 ⑥ Optional
 S : SMD
 R : with Remote ON/OFF
 Positive logic control
 V : Output voltage setting $\pm 1\%$
 N : Auto restart from thermal protection

MODEL	CES24033-25	CES24050-16	CES24120-6	CES24150-4
MAX OUTPUT WATTAGE[W]	82.5	80.0	72.0	60.0
DC OUTPUT	3.3V 25A	5V 16A	12V 6A	15V 4A

SPECIFICATIONS

	MODEL	CES24033-25	CES24050-16	CES24120-6	CES24150-4
INPUT	VOLTAGE[V]	DC18 - 36			DC20 - 33
	CURRENT[A]	3.78typ	3.67typ	3.30typ	2.75typ
	EFFICIENCY[%]	91typ	91typ	91typ	91typ
	START-UP VOLTAGE[V]	DC16 - 18			DC18 - 20
	HYSTERESIS VOLTAGE[V]	DC1 min			
OUTPUT	VOLTAGE[V]	3.3	5	12	15
	CURRENT[A]	25	16	6	4
	LINE REGULATION[mV]	$\pm 5\text{max}$	$\pm 5\text{max}$	$\pm 12\text{max}$	$\pm 15\text{max}$
	LOAD REGULATION[mV]	$\pm 5\text{max}$	$\pm 5\text{max}$	$\pm 12\text{max}$	$\pm 15\text{max}$
	RIPPLE	[mVrms]	20max	20max	40max
		[mVp-p]	60max	80max	120max
	RIPPLE NOISE[mVp-p]	100max	120max	150max	150max
	TEMPERATURE REGULATION[mV]	66max	100max	240max	300max
	DRIFT[mV]	16max	20max	40max	50max
	START-UP TIME[ms]	200max (DCIN 24V, $I_o=100\%$)			
PROTECTION CIRCUIT AND OTHERS	OUTPUT VOLTAGE ADJUSTMENT RANGE	Fixed (TRM pin open), adjustable by external resistor -15% / +15%			
	OUTPUT VOLTAGE SETTING	$\pm 1.6\%$			
	OVERCURRENT PROTECTION	Works over 105% of rating, low voltage protection (shut down) function is built-in.			
	OVERVOLTAGE PROTECTION	125% - 135%	125% - 135%	117% - 127%	
	REMOTE SENSING	Provided			
	REMOTE ON/OFF	Provided (Negative logic L : ON, H : OFF)			

	Standard type							High wattage type		
MODEL	CES48015-30	CES48018-30	CES48025-25	CES48033-25	CES48050-16	CES48120-6	CES48150-4	CES48033-30	CES48050-20	CES48060-17
MAX OUTPUT WATTAGE[W]	45.0	54.0	62.5	82.5	80.0	72.0	60.0	99.0	100.0	102.0
DC OUTPUT	1.5V 30A	1.8V 30A	2.5V 25A	3.3V 25A	5V 16A	12V 6A	15V 4A	3.3V 30A	5V 20A	6V 17A

SPECIFICATIONS

INPUT	MODEL	CES48015-30	CES48018-30	CES48025-25	CES48033-25	CES48050-16	CES48120-6	CES48150-4	CES48033-30	CES48050-20	CES48060-17	
	VOLTAGE[V]	DC36 - 76						DC40 - 60	DC36 - 76			
	CURRENT[A]	*1 1.1typ	1.3typ	1.45typ	1.89typ	1.84typ	1.65typ	1.37typ	2.29typ	2.32typ	2.36typ	
	EFFICIENCY[%]	*1 86typ	87typ	90typ	91typ	91typ	91typ	91typ	90typ	90typ	92typ	
	START-UP VOLTAGE[V]	DC32 - 36						DC36 - 40	DC32 - 36			
	HYSTERESIS VOLTAGE[V]	DC2 min										
OUTPUT	VOLTAGE[V]	1.5	1.8	2.5	3.3	5	12	15	3.3	5	6	
	CURRENT[A]	30	30	25	25	16	6	4	30	20	17	
	LINE REGULATION[mV]	±5max	±5max	±5max	±5max	±5max	±12max	±15max	±5max	±5max	±5max	
	LOAD REGULATION[mV]	±5max	±5max	±5max	±5max	±5max	±12max	±15max	±5max	±5max	±5max	
	RIPPLE	[mVrms]	*2 20max	20max	20max	20max	25max	40max	40max	20max	25max	25max
		[mVp-p]	*2 60max	60max	60max	60max	80max	120max	120max	60max	100max	100max
	RIPPLE NOISE[mVp-p]	*2 100max	100max	100max	100max	120max	150max	150max	100max	150max	150max	
	TEMPERATURE REGULATION[mV]	*2 66max	66max	66max	66max	100max	240max	300max	66max	100max	100max	
	DRIFT[mV]	*3 16max	16max	16max	16max	20max	40max	50max	16max	20max	20max	
	START-UP TIME[ms]	200max (DCIN 48V, Io=100%)										
PROTECTION CIRCUIT AND OTHERS	OUTPUT VOLTAGE ADJUSTMENT RANGE	Fixed (TRM pin open), adjustable by external resistor -20% / +10%					-15% / +15%	-20% / +10%	-20% / +5%	-15% / +15%	-20% / +10%	
	OUTPUT VOLTAGE SETTING	±1.6%										
	OVERCURRENT PROTECTION	Works over 105% of rating, low voltage protection (shut down) function is built-in.										
	OVERVOLTAGE PROTECTION	117% - 127%				125% - 135%	117% - 127%		125% - 135%		117% - 127%	
	REMOTE SENSING	Provided										
	REMOTE ON/OFF	Provided (Negative logic L : ON, H : OFF)										

GENERAL SPECIFICATIONS

ISOLATION	INPUT-OUTPUT	DC1,500V or AC1,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (20 $\pm$ 15 $^{\circ}$ C)
ENVIRONMENT	OPERATING TEMP., HUMID. AND ALTITUDE	-40 to +85 $^{\circ}$ C, 20 - 95%RH (Non condensing) (Refer to DERATING CURVE), 3,000m (10,000feet) max
	STORAGE TEMP., HUMID. AND ALTITUDE	-40 to +100 $^{\circ}$ C, 20 - 95%RH (Non condensing), 9,000m (30,000feet) max (Option S: Refer to the instruction Manual)
	VIBRATION	10 - 55Hz, 49.0m/s 2 (5G), 3minutes period, 60minutes each along X, Y and Z axis
SAFETY	IMPACT	196.1m/s 2 (20G), 11ms, once each along X, Y and Z axis
OTHERS	AGENCY APPROVALS	UL60950-1, C-UL (CSA60950-1), EN60950-1
	CASE SIZE/WEIGHT	57.9 $\times$ 8.5 $\times$ 22.76mm [2.28 $\times$ 0.33 $\times$ 0.9 inches] (W $\times$ H $\times$ D) / 26g max
	COOLING METHOD	Convection / Forced air

*1 At rated input(DC24V,DC48V) and rated load and 25 $^{\circ}$ C, 2m/s.


*2 Ripple and ripple noise is measured by using measuring board with ceramic capacitor 22 μ F. Refer to the Instruction Manual.

*3 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25 $^{\circ}$ C, with the input voltage held constant at the rated input/output.

*4 Refer to the instruction manual for input voltage derating.

External view

1. DIP



2. SMD(options)

