




Connectors > Automotive Connectors > Automotive Housings



Number of Positions: 6

Connector & Housing Type: Housing for Female Terminals

Connector System: Wire-to-Board, Wire-to-Device, Wire-to-Wire

Centerline (Pitch): 5 mm [.197 in]

Sealable: Yes

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Board, Wire-to-Device, Wire-to-Wire
Sealable	Yes
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	6
Number of Rows	1

Electrical Characteristics

Operating Voltage	125 VDC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V, 80 V, 90 V, 125 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Black
Connector & Keying Code	A

Contact Features

--	--



Contact Size	1.8mm
--------------	-------

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA GF
Centerline (Pitch)	5 mm[.197 in]

Dimensions

Product Width	27.6 mm[1.087 in]
Product Length	43.2 mm[1.7 in]
Connector Height	24.8 mm[.98 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	800
Packaging Method	Package

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant







China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 184154-1 2 POS. END CAP HSG., KEY D	 TE Part # 184167-1 2 POS. CAP HSG., KEY E	 TE Part # 184160-1 2 POS. END CAP HSG., KEY K	 TE Part # 184162-1 2 POS. END CAP HSG., KEY M
 TE Part # 184375-1 2 POS PLUG ASSY W/ SIDECAP PRO	 TE Part # 184289-1 RECPT, CONTACT 070, AUPHBZ	 TE Part # 184216-1 2 POS. PLUG ASSY., KEY C	 TE Part # 184169-1 2 POS. CAP HSG., KEY G



TE Part # 184136-1
6 POS./4 CIRC. PLUG ASSY,KEY D



TE Part # 184152-1
2 POS. END CAP HSG., KEY B



TE Part # 172748-1
E-J MK-2 070 CAVITY PLUG



TE Part # 184373-2
CONTACT, RECEPTACLE, .070 TYPE



TE Part # 184171-1
2 POS. CAP HSG., KEY J



TE Part # 184170-1
2 POS. CAP HSG., KEY H



TE Part # 184220-1
2 POS. PLUG ASSY, KEY E



TE Part # 184014-3
2 POS. PLUG ASSY, KEY H, BROWN



TE Part # 184061-1
6 POS/6 CIRC PLUG HSG, KEY A



TE Part # 184000-3
2 POS. PLUG ASSY, KEY A, NAT



TE Part # CAT-EC7491-T273
Econoseal Receptacles and Tabs




TE Part # 184116-1
2 POS. PLUG ASSY, KEY H 1/2

Also in the Series | Sealed Sensor Connector SSC System



Automotive Connector Caps & Covers (2)



Automotive Connector Locks & Position Assurance(2)



Automotive Housings(34)



Automotive Terminals(5)



Connector Seals & Cavity Plugs(4)



Insertion & Extraction Tools(1)

Customers Also Bought





TE Part #184344-1
2X2 PLG ASY KEY A C3




TE Part #184032-1
3 POS. PLUG ASSY, KEY A



TE Part #DRC26-60S06
PLG, 60P, BLK, N, 06




TE Part #5-968220-5
MQS0,63 Au rec CB unseal. 0,2-0,35




TE Part #CAT-M9194-T273
MULTILOCK, RECEPTACLE AND TAB



TE Part #184139-1
WIRE SEAL,RUBBER,SENSOR,BLUE



TE Part #154740-1
PIN .175 DIA REC 20-16AWG PB



TE Part #1438246-4
SPLICE, BUTT, HEATER WIRE 18-16 AWG BR

TE Part #4-1437287-7
MERTEC 32 W PLUG 130025603205

Documents

Product Drawings
6 POS./6 CIRC PLUG ASSY, KEY A
English

CAD Files
3D PDF
English
Customer View Model
ENG_CVM_184060-1_C.2d_dxf.zip
English
Customer View Model
ENG_CVM_184060-1_C.3d_igs.zip
English
Customer View Model
ENG_CVM_184060-1_C.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Positioning the Double Lock Plate

English