

## Specifications for BMP51/53 Labelmaker Labels

<b>Adhesive</b>	Permanent Acrylic
<b>After Process</b>	Yes, this material will work with this application
<b>Application</b>	Automation & Electrical Component Markers; Control Panel & Electrical Panel Labels; Rating & Nameplate Labels
<b>Approval/Compliance</b>	UL Recognised; CSA Accepted; Halogen Free (DIN VDE 0472/part 815)
<b>Article No.</b>	143278
<b>Board Application</b>	Through Hole - Top
<b>Brady Material No.</b>	<a href="#">B-428</a>
<b>Material Type</b>	Metallised Polyester
<b>Brand</b>	MetaLabel™ Series
<b>Colour</b>	Black on Silver
<b>Finish</b>	Matt
<b>Description</b>	Excellent for serial and rating plate applications with nameplate quality and a metal looking finish. Withstands solvents and variable temperatures. polyester with matt finish. Please Note: This material is UL, CSA & AGA approved with its respective ribbon.
<b>Max. Service Temp. °C</b>	120
<b>Order Reference</b>	M-29-428
<b>Printer Compatibility</b>	BMP51; BMP53
<b>Shape</b>	Rectangle
<b>Size - Height (mm)</b>	12.70
<b>Size - Width (mm)</b>	38.10
<b>Surface Mount Technology SMT</b>	No, this material does not work with this application
<b>Through Hole Technology</b>	Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No
<b>Total Qty per Pack</b>	360 Label(s) / Box
<b>Industry</b>	Data & Telecommunications;Electrical;General Industry;Manufacturing;Process
<b>Min. Service Temp. °C</b>	-40

