

Eaton 1713624

Catalog Number: 1713624

Eaton LPC Fixing rating plug 16A

General specifications



Product Name	Catalog Number
Eaton LPC Accessory Adapter plate	1713624
EAN	Product Length/Depth
8711426532007	95 mm
Product Height	Product Width
2 mm	76 mm
Product Weight	Compliances
1.6 g	CE

Product specifications

Type

Adapter plate

10.10 Temperature rise

Not applicable.

10.11 Short-circuit rating

Not applicable.

10.12 Electromagnetic compatibility

Not applicable.

10.13 Mechanical function

Not applicable.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be

Resources

Catalogs

[Eaton-industrial-switch-disconnectors-catalogue-ca008011en-en-gb.pdf](#)

[Product Range Catalog Industrial switch-disconnectors](#)

Declarations of conformity

[DA-DC-00004909.pdf](#)

[DA-DC-00004876.pdf](#)

Installation instructions

[IL008052ZU](#)

evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Frame

DII

Color

Gray

Ambient operating temperature - max

50 °C

Ambient operating temperature - min

-25 °C

Equipment heat dissipation, current-dependent P_{vid}

0 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0 W

Rated operational current (I_e) - max

16 A

Rated operational current for specified heat dissipation (I_n)

0 A

Static heat dissipation, non-current-dependent P_{vs}

0 W



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia