

Rittal – The System.

Faster – better – everywhere.

► Polycarbonate enclosures PK without knockouts – PK 9516.100

Date : Apr 27, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Polycarbonate enclosures PK without knockouts – PK 9516.100

created: 27.04.2021 build on www.rittal.com/uk-en



Product description

Applications: Ambient temperature range: -35 °C...+80 °C
The specified temperatures may be limited by the installed equipment

Material: Enclosure: Fibreglass-reinforced polycarbonate
Cover transparent: Polycarbonate, all-round foamed-in PU seal
Cover screws: Polyamide
Insulating bungs: Polyethylene

Colour: RAL 7035

**Protection category
IP to IEC 60 529:** IP 66

**Protection category
NEMA:** NEMA 4X

IK Code: IK08

Supply includes: Enclosure with cover
Cover screws
Insulating bungs for wall mounting screws

Basic material: Polycarbonate

Product description

Dimensions: Width: 180 mm
Height: 110 mm
Depth: 165 mm

Cover:	transparent
Ambient temperature range:	-35 °C...+80 °C
Packs of:	2 pc(s).
Weight/pack:	1.31 kg
EAN:	4028177139596
Customs tariff number:	94037000
ETIM 7.0:	EC000261
ETIM 6.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 6.0/6.1:	27180101
Product description:	PK Polycarbonate enclosure, WHD: 180x110x165 mm, fibreglass-reinforced polycarbonate, without knockouts, with transparent cover
Approvals	
Approvals:	C-UL DNV-GL UL
Certificates:	NA
Declarations:	Declaration of conformity