

Technical data


1222

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
d - Internal diameter	110 mm
D - External diameter	200 mm
B - Bearing/Inner ring width	38 mm
d1 - External diameter inner ring	140,6 mm
D1 - Inner diameter outer ring	173,1 mm
rs - Min fillet radius	2,1 mm
Radial clearance class	CN
Precision class	P0
Mass	5,32 kg

PRODUCT PERFORMANCE

C - Dynamic load	87000000 mN
C0 - Static load	38600000 mN
Cu - Fatigue limit load	1400000 mN
e - Coefficient	0.17
Y0 - Static axial load coefficient	3.82
Y1 - Lower axial load coefficient	3.64
Y2 - Upper axial load coefficient	5.64
N ref - Reference thermal speed	25800 °/s
N lim - Mechanical Limit Speed	25800 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K



BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	8.739 Hz
BPFI - Over rolling frequency on inner (60 rpm)	11.261 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	7.754 Hz
BRF - Rotational frequency - rolling element (60 rpm)	3.877 Hz
FTF - Rotational frequency - cage (60 rpm)	0.437 Hz

ABUTMENT

da min - Min shoulder diameter IR	121 mm
Da max - Max shoulder diameter OR	189 mm
ra max - Max shaft & housing fillet radius	2 mm

