

Cable marker label - MM-WML 3 (EX10)R C1 WH/BK - 0803931

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Cable marker label, Roll, white, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K: without print, mounting type: adhesive, lettering field size: continuous x 10 mm

Your advantages

- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- Thanks to the continuous format, a wrap-around label of the appropriate width can be created flexibly for the relevant application
- ☑ Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- Mo visible difference between retrospective marking and existing markings created with a desktop roll printer
- The transparent protective foil is wound over the marking and provides permanent protection against contamination and abrasion
- 🗹 The wrap-around labels do not add bulk, which means that the cable can still be drawn through cable ducts, for example
- ▼ The material is cUL certified



Key Commercial Data

Packing unit	1 pc
GTIN	4 055626 212111
GTIN	4055626212111
Weight per Piece (excluding packing)	77.300 g
Custom tariff number	96121010
Country of origin	China
Sales Key	BG221E

Technical data

Dimensions

Length (b)	6.5 m
Width (a)	18 mm
Cable diameter	to 3 mm

Ambient conditions

Ambient temperature (operation)	-40 °C 80 °C



Cable marker label - MM-WML 3 (EX10)R C1 WH/BK - 0803931

Technical data

Ambient conditions

Recommended storage conditions	21 °C / 50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
--------------------------------	---

General

Color	white
Туре	Label
Components	Free from silicone and cadmium
Material	Vinyl polymer
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	without print
Marking mounting type	adhesive
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Test for wipe resistance of inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 11.0	27281102
eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 9.0	27400401



Cable marker label - MM-WML 3 (EX10)R C1 WH/BK - 0803931

Classifications

ETIM

ETIM 6.0 EC001530	0
ETIM 7.0 EC001530	0

UNSPSC

UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized



http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

MH48542

Phoenix Contact 2021 @ - all rights reserved http://www.phoenixcontact.com