

TRICOTRIL® 736



APPLICATION:

- Handling of contaminated heavy parts
- Cleaning and maintenance in chemical plants
- Galvanising works
- Petrochemistry
- Chemical industry

QUALITIES AND ADVANTAGES:

- Broad chemical resistance
- High mechanical resistance
- Good grip when handling greasy and oily parts
- High user comfort for long working periods without operator fatigue
- Skin friendly due to solvent-free adhesive on the cotton liner

FEATURES:

- AQL < 0,65
- Free from natural latex
- Cotton liner is fixed later to the finished glove, to ensure maximum protection
- Seamless cotton liner
- Food safety according to EU 1935/2004



CHEMICAL PROTECTIVE GLOVES

ATTRIBUTE	DESCRIPTION / VALUES
Article No. Name	• 736 • Tricotril® 736
Material	• Nitrile • Cotton
Description	• Seamless cotton liner • Cuff, fully coated • Palm profile
Length (mm)	• 290 -310
Total thickness (mm)	• 1,5 ± 0,2
Coating thickness (mm)	• 0,4
Colour	• Green
Size	• 8,9,10,11
Classification	• Category III EN 388:2016 3121X EN 374-1/Type A AJKLOPT EN 374-5 Virus

HONEYWELL PPE
KCL GmbH
Industriepark Rhoen
Am Kreuzacker 9
36124 Eichenzell, Germany
Phone: +49 69 80885425
kclorders@honeywell.com
sps.honeywell.com

Honeywell KCL Tricotril Data Sheet - 01/2023
© 2023 Honeywell International Inc.

