




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2025/03/20	Henry	New Initial.





✓ Laser Marking




—(QC)M20*1.5

—O-Ring 23*1.5



Recommended
installation orientation

建議安裝朝向



Threaded Hole

Polish:

✓M20*1.5

Recommended Panel Cut-Out

建議開孔尺寸

Note:

- *  Important Dimension.
- * Waterproof Rate: IP68(2m/1h)
- * Body: Aluminum Alloy, Anodizing
- * Membrane: ePTFE
- * O-Ring: Rubber, Black.
- * Spring: SUS304
- * Air Permeability: >500ml/min at 1.5 kPa
- * Opening Pressure: 6 ± 1.5 kPa
- * Recommended Torque: 4.0~5.0 N.m
- * Breaking Torque: >20 N.m
- * Recommended Plate Thickness: $T \geq 3.75$ mm

UNIT: mm			TITLE RELIEF VENT. METAL, M20 >500ML/MIN@1.5KPA, ME			Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO VT-RMM20ME-NO8001	DRAWN BY Henry	DATE 2025-03-20
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°	SCALE 3:2			SIZE A4	SHEET 1 OF 1		DWG NO VT-RMM20ME-NO8001	CHECKED BY Jerry	DATE 2025-03-20
REV. A			WC-REV. .0	QC: Inspection item			CUSTOMER ALTW	APPROVED BY Fred	DATE 2025-03-20