


Features

- Flush cutter with special INDUCTION-hardened cutting edges.
- For copper wire Ø 1.30mm (16 awg)
- For iron wire Ø 1.02mm (18 awg)
- Steel thickness 3mm.
- ESD-safe
- Anti-reflection phosphating surface treatment
- Anti-slip bi-material dolphin handle with light and comfortable grip
- Made in Italy

RS PRO ESD Safe Flush Cutter, Induction-Hardened Cutting Edges, Medium

RS Stock No.: 0616313



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Buy this product from <https://uk.rs-online.com/>

Page 1 of 2

RS PRO ESD Safe Flush Cutters

RS PRO cutter has flush cutter with special INDUCTION-hardened cutting edges.
For copper wire Ø 1.30mm (16 awg) and iron wire Ø 1.02mm (18 awg).
Steel thickness 3mm. Tool is equipped with a return spring designed to have a constant force, thus reducing operator effort.

ESD-safe version. Made with high carbon steel and undergo a controlled atmosphere heat treatment. The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.

The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator.

General Specifications

Cutter Type	Flush cutter
Materials Cut	Copper wire Ø 1.30mm (16 awg) Iron wire Ø 1.02mm (18 awg)
No Sparking	No
Overall Length	141mm +/- 2mm
VDE/1000V Approved	No
Height Safe	No
ESD Safe	Yes
Material	High Carbon Steel
Maximum Cutting Capacity	1.30mm
Cut Type	Flush

Approvals

Declarations	REACH DoC
Standards Met	IEC 61340-5-1 (ESD)

