

HIGH CUT RESISTANT IMPACT GLOVE WITH ROBUST AND FLEXIBLE IMPACT PANEL

A flexible seamless impact cut resistant glove level F/A6 with sandy nitrile on the palm to maximize grip. Ergonomic TPR design allows outstanding flexibility

FEATURES

- › Cut resistance: level F (EN388:2016) / ANSI A6
- › 13 gauge engineered HPPE liner offers great dexterity for fine handling
- › Free from glass and steel fibre for reduced risks of irritation
- › Excellent grip with a nitrile foam sandy coating on the palm
- › Dense, moulded TPR protection zones on knuckles, fingers, thumb and back of hand
- › Reinforced thumb crotch enhances durability
- › Ergonomically designed TPR follow the hand movement reducing hand fatigue
- › TPR zones are sewn to the liner for increased resistance
- › Touchscreen capabilities to allow usage with screen devices
- › Contact heat protection up to 100°C / 212°F for a short period (15 sec max)



SUITABLE FOR


Typical Industries

- Oil and Gas
- Construction
- Mining
- Transport
- Heavy Engineering
- Offshore
- Ports

Suitable Applications

- Demolition
- Drilling
- Extraction
- Heavy handling
- Cargo handling
- Extraction and refining
- Rigging

CERTIFICATION



See overleaf for explanation

PRODUCTION INFORMATION

MATERIALS	LINER:	13 gauge engineered HPPE
	COATING:	Foam nitrile
COLOUR	Black	
LENGTH (mm)	250 (Size Dependent)	
CUFF STYLE	Elasticated knit wrist	

ORDERING DETAILS

SIZE	CODE	PACKAGING
7/S	SKG00083FD	10 pairs per bag
8/M	SKG00083FF	
9/L	SKG00083FH	
10/XL	SKG00083FJ	60 pairs per case
11/XXL	SKG00083FL	
12/XXXL	SKG00083FN	


RECOMMENDATIONS FOR USE

- USE: General handling glove with cut and impact protection. Not suitable for thermal, electrical, chemical protection. Do not use near moving machines if there is a risk of entanglement
- STORAGE: Store in dry conditions in the original packaging and away from direct sunlight
- CLEANING: To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present
- LIFETIME: Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use

CERTIFICATION LEGENDS



MECHANICAL HAZARDS EN 388:2016
PERFORMANCE LEVELS*



*If tests are not performed or are not applicable, 'X' will be placed instead of a number/letter



HEAT AND FIRE
EN 407

PERFORMANCE LEVELS



CLASSIFICATION FOR CUT RESISTANCE

Measured breakthrough time	Permeation performance index (grams)
A1	≥ 200
A2	≥ 500
A3	≥ 1000
A4	≥ 1500
A5	≥ 2200
A6	≥ 3000
A7	≥ 4000
A8	≥ 5000
A9	> 6000

CLASSIFICATION FOR IMPACT RESISTANCE

Performance level	Mean (kN)	All impacts (kN)
1	≤ 9	< 11.3
2	≤ 6.5	≤ 8.1
3	≤ 4	≤ 5

ANSI/ISEA PUNCTURE RESISTANCE

ANSI Puncture Level	Puncture Resistance (newtons)
1	10-19
2	20-59
3	60-99
4	100-149
5	150+

Puncture Resistance (ANSI/ISEA 105): Puncture resistance is determined by the max force that it takes, exerted from a probe, to puncture the fabric.

ANSI/ISEA 105-2016 ABRASION RATING CHART

Abrasion Level Rating	0	1	2	3	4	5	6
Gram Load	500	500	500	500	1000	1000	1000
Abrasion Cycles to Fail	<100	≥100	≥500	≥1,000	≥3,000	≥10,000	≥20,000

GLOBUS

EUROPE

www.globusgroup.com

E: sales@globus.co.uk

T: +44 (0)161 877 4747

F: +44 (0)161 877 4746

MIDDLE EAST & AFRICA

www.globusgroup.com/gcc

E: gcc@globusgroup.com

T: +971 4 882 9962

F: +971 4 882 9963

GLOBUS AMERICAS

www.globusgroup.com

E: americas@globusgroup.com

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
 Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
 Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

EU Type-Examination Certificate issued by CCQS Certification Services Limited, Block 1 Blanchardstown Corporate Park, Ballycoolin Road, Blanchardstown, Dublin, D15 AKK1, Ireland (Notified Body No 2834)

© 2024 Globus (Shetland) Ltd | SKY-DATA-TORQ-BORA-0724_1

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.