

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.11.2020
1.13	06.01.2021	100000019443	Date of first issue: 29.01.2019

---

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier

Trade name : KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Product code : 6135

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Substance/Mixture : Air Freshener

#### 1.3 Details of the supplier of the safety data sheet

Company name of supplier : Kimberly-Clark Europe Limited

Address : 40 London Road  
Reigate  
Surrey RH2 9QP  
United Kingdom

Telephone : +44 1737 736000

E-mail address of person responsible for the SDS : sdscontact@kcc.com

Emergency telephone number : +44 1865 407333

Poison Center Name : NHS 111

Poison Center Telephone : 111

---

### SECTION 2: Hazards identification

#### 2.1 Classification of the substance or mixture

##### Classification (REGULATION (EC) No 1272/2008)

Eye irritation, Category 2 H319: Causes serious eye irritation.

#### 2.2 Label elements

##### Labelling (REGULATION (EC) No 1272/2008)

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version 1.13      Revision Date: 06.01.2021      SDS Number: 100000019443      Date of last issue: 10.11.2020  
Date of first issue: 29.01.2019

Hazard pictograms :



Signal word : Warning

Hazard statements : H319 Causes serious eye irritation.

Precautionary statements : **Response:**  
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P337 + P313 If eye irritation persists: Get medical advice/attention.

### Additional Labelling

EUH208 Contains 4-tert-butylcyclohexyl acetate. May produce an allergic reaction.

### 2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

## SECTION 3: Composition/information on ingredients

### 3.2 Mixtures

#### Hazardous components

Chemical name	CAS-No. EC-No. Index-No. Registration number	Classification	Concentration (% w/w)
Butanol, 3-methoxy-3-methyl-	56539-66-3 260-252-4	Eye Irrit. 2; H319	>= 5 - < 10
propan-2-ol	67-63-0 200-661-7 603-117-00-0	Flam. Liq. 2; H225 Eye Irrit. 2; H319 STOT SE 3; H336	>= 5 - < 10
4-tert-butylcyclohexyl acetate	32210-23-4 250-954-9	Skin Sens. 1B; H317	>= 0.1 - < 1

For explanation of abbreviations see section 16.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.11.2020
1.13	06.01.2021	100000019443	Date of first issue: 29.01.2019

---

### SECTION 4: First aid measures

#### 4.1 Description of first aid measures

General advice : No hazards which require special first aid measures.

Protection of first-aiders : Not applicable

If inhaled : Not required under normal use.

In case of skin contact : Wash off with soap and plenty of water.  
If skin irritation persists, call a physician.

In case of eye contact : Immediately flush eye(s) with plenty of water.

If swallowed : Do NOT induce vomiting.

#### 4.2 Most important symptoms and effects, both acute and delayed

Symptoms : No information available.

#### 4.3 Indication of any immediate medical attention and special treatment needed

Treatment : No information available.

---

### SECTION 5: Firefighting measures

#### 5.1 Extinguishing media

Suitable extinguishing media : Alcohol-resistant foam  
Carbon dioxide (CO<sub>2</sub>)  
Dry chemical

Unsuitable extinguishing media : Do NOT use water jet.

#### 5.2 Special hazards arising from the substance or mixture

Specific hazards during firefighting : No special precautions required.

Hazardous combustion products : No hazardous combustion products are known

#### 5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.

---

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.11.2020
1.13	06.01.2021	100000019443	Date of first issue: 29.01.2019

---

Further information : Use water spray to cool unopened containers.

Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.

---

### SECTION 6: Accidental release measures

#### 6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Ensure adequate ventilation.  
Remove all sources of ignition.

#### 6.2 Environmental precautions

Environmental precautions : Prevent product from entering drains.

#### 6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Wipe up with absorbent material (e.g. cloth, fleece).

#### 6.4 Reference to other sections

For personal protection see section 8.

---

### SECTION 7: Handling and storage

#### 7.1 Precautions for safe handling

Advice on safe handling : No special handling advice required.

Advice on protection against fire and explosion : Keep product and empty container away from heat and sources of ignition.

Hygiene measures : General industrial hygiene practice.

#### 7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep container tightly closed in a dry and well-ventilated place.

Advice on common storage : No special restrictions on storage with other products.

Further information on storage stability : No decomposition if stored and applied as directed.

#### 7.3 Specific end use(s)

Specific use(s) : Air Freshener

---

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version 1.13      Revision Date: 06.01.2021      SDS Number: 100000019443      Date of last issue: 10.11.2020  
Date of first issue: 29.01.2019

### SECTION 8: Exposure controls/personal protection

#### 8.1 Control parameters

##### Occupational Exposure Limits

Components	CAS-No.	Value type (Form of exposure)	Control parameters	Basis
propan-2-ol	67-63-0	TWA	400 ppm 999 mg/m <sup>3</sup>	GB EH40
		STEL	500 ppm 1,250 mg/m <sup>3</sup>	GB EH40

#### 8.2 Exposure controls

##### Personal protective equipment

Eye protection : Not required under normal use.

Hand protection  
Remarks : not required under normal use

Skin and body protection : not required under normal use

Respiratory protection : Not required under normal use.

Protective measures : No special protective equipment required.

### SECTION 9: Physical and chemical properties

#### 9.1 Information on basic physical and chemical properties

Appearance : liquid

pH : No information available.

Melting point/freezing point : 0 °C

Boiling point/boiling range : 100 °C

Flash point : 46 °C

Flammability (solid, gas) : Not classified as a flammability hazard

Upper explosion limit / Upper flammability limit : No data available

Lower explosion limit / Lower flammability limit : No data available

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.11.2020
1.13	06.01.2021	100000019443	Date of first issue: 29.01.2019

---

Vapour pressure : No data available

Solubility(ies)  
Water solubility : completely soluble

### 9.2 Other information

Flammability (liquids) : Does not sustain combustion., Not classified as supporting combustion according to the transport regulations.

---

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

Stable under recommended storage conditions.

### 10.2 Chemical stability

No decomposition if stored and applied as directed.

### 10.3 Possibility of hazardous reactions

Hazardous reactions : Vapours may form explosive mixture with air.

### 10.4 Conditions to avoid

Conditions to avoid : Heat, flames and sparks.

### 10.5 Incompatible materials

Materials to avoid : Strong acids and oxidizing agents

### 10.6 Hazardous decomposition products

Stable under recommended storage conditions.

---

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute toxicity

#### Components:

#### propan-2-ol:

Acute oral toxicity : LD50 Oral (Rat): 5,840 mg/kg  
Method: OECD Test Guideline 401  
GLP: no  
Remarks: See User Free Text

LD50 Oral (Rat): 1,870 mg/kg

Acute inhalation toxicity : LC50 (Rat, male and female): > 10000 ppm  
Exposure time: 6 h

---

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.11.2020
1.13	06.01.2021	100000019443	Date of first issue: 29.01.2019

---

Test atmosphere: vapour  
Method: OECD Test Guideline 403  
GLP: yes

LC50 (Rat): 72,600 mg/m<sup>3</sup>  
Exposure time: 4 h

Acute dermal toxicity : LD50 Dermal (Rabbit): 12,800 mg/kg  
Method: OECD Test Guideline 402  
GLP: no  
Remarks: See User Free Text

LD50 Dermal (Rabbit): 4,059 mg/kg

### Skin corrosion/irritation

#### Product:

Remarks : According to the classification criteria of the European Union, the product is not considered as being a skin irritant.

#### Components:

##### propan-2-ol:

Species : Rabbit  
Exposure time : 4 hrs  
Method : No information available.  
Result : No skin irritation  
GLP : no  
Remarks : See User Free Text

##### 4-tert-butylcyclohexyl acetate:

Species : human skin  
Result : No skin irritation

### Serious eye damage/eye irritation

#### Product:

Assessment : Irritating to eyes.

#### Components:

##### Butanol, 3-methoxy-3-methyl-:

Assessment : Irritating to eyes.

##### propan-2-ol:

Species : Rabbit  
Method : OECD Test Guideline 405

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.11.2020
1.13	06.01.2021	100000019443	Date of first issue: 29.01.2019

---

Result : Irritating to eyes.  
GLP : no

### Respiratory or skin sensitisation

#### Product:

Assessment : Does not cause skin sensitisation.

#### Components:

##### **propan-2-ol:**

Test Type : Buehler Test  
Exposure routes : epicutaneous  
Species : Guinea pig  
Method : OECD Test Guideline 406  
Result : Did not cause sensitisation on laboratory animals.  
GLP : yes

### Germ cell mutagenicity

#### Product:

Germ cell mutagenicity-  
Assessment : Contains no ingredient listed as a mutagen

#### Components:

##### **propan-2-ol:**

Genotoxicity in vitro : Test Type: In vitro mammalian cell gene mutation test  
Test system: Chinese hamster ovary cells  
Concentration: 0.0098, 0.0195, 0.0391, 0.0781  
Metabolic activation: with and without metabolic activation  
Method: OECD Test Guideline 476  
Result: Negative for genotoxicity  
GLP: yes

Genotoxicity in vivo : Test Type: Micronucleus test  
Species: Mouse (male and female)  
Strain: ICR  
Cell type: Bone marrow  
Application Route: Intraperitoneal injection  
Exposure time: Single exposure  
Dose: 350, 1173 and 3500 mg/kg bw  
Method: OECD Test Guideline 474  
Result: negative  
GLP: yes





# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.11.2020
1.13	06.01.2021	100000019443	Date of first issue: 29.01.2019

---

### STOT - single exposure

**Product:**

Remarks : No data available

### STOT - repeated exposure

**Product:**

Remarks : No data available

### Repeated dose toxicity

**Components:**

**propan-2-ol:**

Species : Rat, male and female  
NOAEL : parts per million, 5000 parts per million  
Application Route : Inhalation  
Test atmosphere : vapour  
Exposure time : 6 hours/day  
Number of exposures : 5 days/week for 104 weeks  
Dose : 0, 500, 2500, 5000 ppm  
Group : yes  
Method : See User Free Text  
GLP : yes

### Further information

**Product:**

Remarks : Health injuries are not known or expected under normal use.  
Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting.

---

## SECTION 12: Ecological information

### 12.1 Toxicity

**Product:**

Toxicity to fish : Remarks: No information available.

Toxicity to daphnia and other aquatic invertebrates : Remarks: No information available.

Toxicity to algae/aquatic plants : Remarks: No information available.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.11.2020
1.13	06.01.2021	100000019443	Date of first issue: 29.01.2019

---

### Components:

#### **Butanol, 3-methoxy-3-methyl-:**

Toxicity to fish : LC50 (*Oryzias latipes* (Orange-red killifish)): > 100 mg/l  
Exposure time: 96 h  
Test Type: semi-static test

#### **propan-2-ol:**

Toxicity to fish : LC50 (*Pimephales promelas* (fathead minnow)): 9,640 mg/l  
End point: mortality  
Exposure time: 96 h  
Test Type: flow-through test  
Analytical monitoring: yes  
Method: OECD Test Guideline 203  
GLP: no

LC50 (*Pimephales promelas* (fathead minnow)): 10,000 mg/l  
End point: mortality  
Exposure time: 96 h  
Test Type: flow-through test  
Analytical monitoring: yes  
Method: OECD Test Guideline 203  
GLP: no

LC50 (*Pimephales promelas* (fathead minnow)): 9,640 mg/l  
Exposure time: 96 h  
Test Type: flow-through test

LC50 (*Pimephales promelas* (fathead minnow)): 11,130 mg/l  
Exposure time: 96 h  
Test Type: static test

LC50 (*Lepomis macrochirus* (Bluegill sunfish)): > 1,400,000 µg/l  
Exposure time: 96 h

Toxicity to daphnia and other aquatic invertebrates : EC50 (*Daphnia magna* (Water flea)): 9,714 mg/l  
Exposure time: 24 h  
Test Type: static test  
Method: OECD Test Guideline 202  
GLP: no

EC50 (*Daphnia magna* (Water flea)): 13,299 mg/l  
Exposure time: 48 h

Toxicity to algae/aquatic plants : EC10 (*Scenedesmus quadricauda* (Green algae)): 1,800 mg/l  
End point: See User Free Text  
Exposure time: 168 h  
Test Type: static test  
Analytical monitoring: no

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.11.2020
1.13	06.01.2021	100000019443	Date of first issue: 29.01.2019

---

Method: See User Free Text  
GLP: no

EC50 (Desmodesmus subspicatus (green algae)): > 1,000 mg/l  
Exposure time: 96 h

EC50 (Desmodesmus subspicatus (green algae)): > 1,000 mg/l  
Exposure time: 72 h

Toxicity to microorganisms : toxicity threshold (Pseudomonas putida): 1,050 mg/l  
Exposure time: 16 h  
Test Type: static test  
Analytical monitoring: no  
Method: DIN 38 412 Part 8  
GLP: no  
Remarks: See User Free Text

### 12.2 Persistence and degradability

#### Product:

Biodegradability : Remarks: No information available.

#### Components:

##### **4-tert-butylcyclohexyl acetate:**

Biodegradability : Result: Readily biodegradable.

### 12.3 Bioaccumulative potential

#### Product:

Bioaccumulation : Remarks: Does not bioaccumulate.

### 12.4 Mobility in soil

#### Product:

Mobility : Remarks: No information available.

### 12.5 Results of PBT and vPvB assessment

#### Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher..

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.11.2020
1.13	06.01.2021	100000019443	Date of first issue: 29.01.2019

---

### 12.6 Other adverse effects

**Product:**

Additional ecological information : There is no data available for this product.

---

## SECTION 13: Disposal considerations

### 13.1 Waste treatment methods

Product : Dispose of in accordance with local regulations.

Contaminated packaging : Dispose of as unused product.

Do not re-use empty containers.

---

## SECTION 14: Transport information

### 14.1 UN number

Not regulated as a dangerous good

### 14.2 UN proper shipping name

Not regulated as a dangerous good

### 14.3 Transport hazard class(es)

Not regulated as a dangerous good

### 14.4 Packing group

Not regulated as a dangerous good

### 14.5 Environmental hazards

Not regulated as a dangerous good

### 14.6 Special precautions for user

Not applicable

### 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable for product as supplied.

---

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

**The components of this product are reported in the following inventories:**

REACH : This mixture contains only ingredients which have been registered according to Regulation (EC) No. 1907/2006 (REACH).

---

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.11.2020
1.13	06.01.2021	100000019443	Date of first issue: 29.01.2019

### 15.2 Chemical safety assessment

#### SECTION 16: Other information

##### Full text of H-Statements

H225 : Highly flammable liquid and vapour.  
H317 : May cause an allergic skin reaction.  
H319 : Causes serious eye irritation.  
H336 : May cause drowsiness or dizziness.

##### Full text of other abbreviations

Eye Irrit. : Eye irritation  
Flam. Liq. : Flammable liquids  
Skin Sens. : Skin sensitisation  
STOT SE : Specific target organ toxicity - single exposure  
GB EH40 : UK. EH40 WEL - Workplace Exposure Limits  
GB EH40 / TWA : Long-term exposure limit (8-hour TWA reference period)  
GB EH40 / STEL : Short-term exposure limit (15-minute reference period)

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TRGS - Technical Rule for

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## KIMBERLY-CLARK PROFESSIONAL\* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 10.11.2020
1.13	06.01.2021	100000019443	Date of first issue: 29.01.2019

---

Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

### Further information

#### Classification of the mixture:

Eye Irrit. 2

H319

#### Classification procedure:

Based on product data or assessment

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

GB / EN