

CG 17-125

Compact angle grinders, Ø 125 mm

Ergonomic 1700 W compact angle grinder with high power reserve for effective sanding and cutting.

Product number: 7 222 81 60 00 0



Details

- > Robust motor for daily use.
- > Long-life thanks to overload protection and long carbon brush service life.
- > Rapid work progress thanks to powerful motor.
- > Extensive user protection provided by kick-back monitoring, restart protection, soft start and anti-vibration handle.
- > Gearbox head can be rotated 90° for high versatility.
- > Abrasive materials can be changed at speed and without the need for any tools: quick-clamping nut included in scope of supply as standard.
- > Good ability to cope with overload thanks to direct motor cooling.
- > Industrial cable H07, length 4m.

Price includes

- ✓ 1 wheel guard
- ✓ 1 anti-vibration handle
- ✓ 1 Tool-free quick-clamping nut
- ✓ 1 key

Product feature

- ✓ Soft start
- ✓ Blockage monitoring
- ✓ Kick-back check
- ✓ Restart protection
- ✓ Electronic overload protection

Application

Roughing-down



Deburring



Dividing



Brushing



★ suitable
★★ well suitable

Technical data

TECHNICAL DATA

Input	1,700 W
Output	1,010 W
Speed, no load	11,500 rpm
Grinding disc Ø	125 mm
Elast. Backing pad Ø	125 mm
Flange	M 14
Cable with plug	4 m
Weight according to EPTA	2.40 kg

VIBRATION AND SOUND EMISSION VALUES

Sound pressure level LpA Uncertainty of measured value KpA	92 dB 3 dB
Sound power level LWA Uncertainty of measured value KWA	103 dB 3 dB
Vibration value 1 α_{hv} 3-way	6 m/s ²
Vibration value 2 α_{hv} 3-way	4 m/s ²
Uncertainty of measured value K α	1,5 m/s ²

Application examples

