


Media Rolls



Advantages

- Available for all kind of applications

Application: For use as a pre filter in air conditioning, and spraybooth ventilation.

Media: Synthetic and glass fiber

EN779:2012 efficiency: G2-M5

Arrestance efficiency: 65% - 92%.

Temperature: 80°C - 100°C maximum in continuous service.

Humidity: 100% RH.

Art. No.	Model	Characteristics	Width	Length	Filter class	Velocity m/s	Pressure drop	Unit volume m ³	Dust holding g/m ²
Synthetic media									
	T15-150		2,05	20	G2	1.5	15	0.53	410
	T15-150		1,0	20	G2	1.5	15	0.26	410
	PST 290		2,05	20	G4	1.10	41	0.82	350
	PST 290		1,0	20	G4	1.10	41	0.40	350
	PST 290		0,76	20	G4	1.10	41	0.30	350
	T15-350		2,05	20	G4	1.5	25	0.62	678
	T15-500		2,05	20	G4	1.6	35	0.08	540
	POLY 50		2,05	20	G3	1.7	45	2.05	550
	POLY SOFT 50		2,0	10	G3	1.8	52	1.00	673
	POLY SOFT 50		2,0	20	G3	1.9	52	2.00	673
	HC - 80		1,0	50	G2	1.10	12	0.50	360
Glass fiber media									
	PR 50		0.710	20	G2	1.8	30	0.71	600
	PR 50		0.710	40	G2	1.8	30	1.42	600
	PR 50		1.0	20	G2	1.8	30	1.00	600
	PR 50		1.0	40	G2	1.8	30	2.00	600
	PR 50		1.5	20	G2	1.8	30	1.5	600
	PR 50		1.5	40	G2	1.8	30	3.00	600
	PR 50		1.829	20	G2	1.8	30	1.829	600
	PR 50		2.0	20	G2	1.8	30	2.00	600
	PR 50		2.0	30	G2	1.8	30	3.00	600
	PR 75		0.71	40	G2	1.8	35	2.13	750
	PR 100		0.762	20	G2	1.8	40	1.524	900
	PR 100		1.0	20	G2	1.8	40	2.00	900
	PR 100		1.0	40	G2	1.8	40	4.00	900
	PR 100		1.524	20	G2	1.8	40	3.048	900
	PR 100		1.524	40	G2	1.8	40	6.096	900
	PR 100		1.829	20	G2	1.8	40	3.658	900
	GR50		0.610	40	G3	1.8	35	1.25	700
	VK25 White	Impregnated	2,00	20	G2	2.5	60		700
	VK50 White	Impregnated	2,00	20	G3	2.5	70		1500
	VK50 Green	Dry	2,00	20	G2	1	25		1200
	SC600T	Impregnated	2,00	20	M5	0.25	48		305

Other sizes and cut pads available on request.