

# ABUS Wired Indoor Siren

Art. no. AZSG10020

Page 1 of 1



- LED to display armed/disarmed status
- Simple, inconspicuous design
- Simple installation
- 90 dB(A) sound pressure @ 1m
- Tamper detection for front and rear sides
- Shock-resistant construction from polycarbonate

The inside siren is installed inside your building. It is the last and critical module of a complete alarm chain. The inside siren is an acoustic signal generator. You have a choice between two alarm modes in this case. Both signals are felt to be extremely loud due to the high acoustic pressure and the signal frequency. The remotely activated LED of the alarm siren can be used to detect the status of the alarm panel (armed/disarmed). The rugged plastic housing of the acoustic signal generator is protected against sabotage by a wall and cover contact. The inside siren is powered with 12 V.

## Technical Data:

Dimensions	(WxHxD) 115x138x36 mm
Width	119 mm
Gross weight	0,212 kg
Housing material	POLYCARBONAT (PC)
Height	41 mm
Length	145 mm
Power consumption	1,2 W
Illuminant	LED
Max. operating temperature	40 °C

Max. humidity	95 %
Min. operating temperature	-15 °C
Installation location	Indoors
Net weight	0,174 kg
Tamper monitoring	Yes
DC voltage supply	12 V
Environmental class	II