



## Bi-directional ESD Protection Diode

**Peak Pulse Power - 400 Watts**  
**Reverse Working Voltage - 5V**

## Description

The H20X25V0B device has been specifically designed to protect sensitive components which are connected to data and transmission lines from overvoltage caused by ESD (electrostatic discharge).

## Features

- 1 Channel of ESD Protection (Bi-directional)
- Peak Pulse Power :P<sub>pp</sub> = 400W (tp=8/20 us)
- Reverse Working Voltage : 5V
- Low Leakage Current
- Low Clamping Voltage
- IEC 61000-4-2 (ESD) :±27kV(Contact) / ±30kV(Air)

## Applications

- Computers and peripherals
- Communication system
- Audio & video equipment
- Portable instrumentation

## Mechanical Data


- Case: DFN1006 Package
- Case Material: "Green" Molding Compound UL Flammability Classification Rating 94V-0
- Component in accordance to RoHS
- Halogen Free

Note: Products with logo  or  are made by HY Electronic (Cayman) Limited.

## Ordering Information


- Package :DFN1006
- Reel Size :7 (inches)
- Quantity Per Reel :10,000/Tape & Reel
- Quantity One Box :100,000/Tape & Reel
- Quantity One Carton :400,000/Tape & Reel

## Marking Information




"H"=Product Type Marking Code

## Package Outline



DFN1006 Top View

## Device Schematic &amp; PIN Configuration



## Maximum Ratings (@TA = +25°C, unless otherwise specified.)

## Absolute Ratings

Parameter	Symbol	Value	Unit
Peak Pulse Power Dissipation (8/20 us)	P <sub>PP</sub>	400	W
Peak Pulse Current (8/20 us)	I <sub>PP</sub>	20	A
ESD Protection- Contact (Standard IEC 61000-4-2)	V <sub>ESD</sub>	±27	k V
ESD Protection- Air (Standard IEC 61000-4-2 )		±30	
Operating Temperature Range	T <sub>J</sub>	-55 to +125	° C
Storage Temperature Range	T <sub>STG</sub>	-55 to +150	° C
Soldering Temperature, t max =10s	T <sub>L</sub>	260	° C

## Electrical Characteristics

Parameter	Test Conditions	Symbol	Min	Typ	Max	Unit
Reverse Working Voltage	---	V <sub>RWM</sub>	-	-	5	V
Reverse Breakdown Voltage	I <sub>T</sub> = 1mA	V <sub>B</sub>	5.6	-	9	V
Reverse Current	V <sub>R</sub> = 5V	I <sub>R</sub>	-	-	1	uA
Reverse Clamping Voltage	I <sub>PP</sub> = 1A (8/20μs)	V <sub>C</sub>	-	-	9.8	V
	I <sub>PP</sub> = 20A (8/20μs)		-	-	20	
Junction Capacitance	V <sub>R</sub> = 0V, F = 1MHz	C <sub>j</sub>	-	30	40	p F



## Rating and Characteristic Curves

FIG.1 - 8/20us Pulse Waveform According to IEC 61000-4-5




FIG.2 - Power Dissipation Versus Pulse Time




FIG.3 - Peak Pulse Power Versus  $T_j$






FIG.4 - Clamping Voltage Characteristic






## Package Outline Dimensions



DFN1006 Package		
Dim	Min	Max
A	0.45	0.55
A1	-	0.02
B	0.95	1.05
C	0.55	0.65
L	0.45	0.55
L1	0.2	0.3
All Dimensions in mm		

Note: HY internal have both AT site

## Suggested Soldering Pad Layout



Dim.	Value
A	1.10
B	0.90
C	0.30
D	0.60
E	0.40
All Dimensions in mm	



## Disclaimer

All specifications and data are subject to be changed without notice to improve reliability function or design or other reasons.

HY makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, HY disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on HY's knowledge of typical requirements that are often placed on HY products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify HY's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, HY products are not designed for use in medical, life-saving, or life-sustaining applications or for any other applications in which the failure of the HY product could result in personal injury or death. Customers using or selling HY products not expressly indicated for use in such applications do so at their own risk. Please contact authorized HY personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of HY. Product names and markings noted herein may be trademarks of their respective owners.