

Heavy Duty Power Connector Inserts & Modules

Features

- 10P+E Female Insert 16A 250V 50-60Hz Screw A Series - 10A Size.
- 10P+E Male Insert 16A 250V 50-60Hz Screw A Series - 10A Size.
- 10A Housing Bulkhead Mount. Alum.Single Lever w/Plastic Latch Grey IP65
- 10A Hood Alum.Single Lever w/o Latch Grey IP65 Side Ent.M20

RS PRO Industrial Power Connectors

RS Stock No.: 457-268



Representative Photo

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Heavy Duty Power Connector Inserts & Modules

Product Description

- Heavy-duty connectors with inserts and aluminum hoods are designed for industrial automation, power distribution, transportation, and harsh environments like mining and construction, ensuring reliable electrical connections in demanding conditions. They are commonly used with industrial cables, control panels, and heavy-duty electrical components such as contactors and relays. However, they are not suited for high-frequency data transmission or light-duty consumer electronics, as they are built for durability rather than delicate signal integrity or small-scale applications.

General Specifications

Flammability acc. to UL 94	V 0
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Material (insert)	Polycarbonate
Material (Contacts)	Brass (Silver Plated)

Mechanical Specifications




Termination	Screw terminal
Cable Entry	Back
Electrical Data	
acc. to EN 61984	10 A 250 V 4 kV 3
Wire gauge	0.75 2.5 mm ²
Stripping Length	7 mm
Tightening Torque	0.5 Nm
Mechanical Working Life	≥500
AWG	18-14
Insulation resistance	≥10 ¹⁰ Ω
Contact Resistance	≤1 mΩ

General Specifications Hoods


Material	Aluminum	Polycarbonate
Colour	RAL 7040 (grey) - RAL 9005 (black)	RAL 7032 (light grey)/ RAL 9005 (black)
Surface	Powder-coated	-
Locking element	Stainless steel	Polyamide


Heavy Duty Power Connector Inserts & Modules

Lever type	Steel	Lever , plastic
Hoods/Housing seal	NBR	NBR
Limiting temperatures	-40 °C... +125 °C	-40 °C... +125 °C
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP65	IP65

RS Pro 10 A 16 A 250 V 4 kV 3		10 A
Male insert (M)	Female insert (F)	 (1) distance for contact max. 24 mm Panel cut out
Part Number:	Part Number:	
  Male	  Female	

Heavy Duty Power Connector Inserts & Modules

RS Pro 16 A Hoods/Housings		10 A
Hood	Cable Entry	
Part Number:	1x M20	
		

RS Pro 16 A Hoods/Housings		10 A
Housing (Surface Mounting)	Cable Entry	
Part Number:	-	
		