



Main

Range	Acti 9
Product name	Acti 9 iRC
Device application	Voltage control relay
Signal contacts composition	1 C/O

Complementary

[Ie] rated operational current	8 A AC 50/60 Hz 250 V cos Phi = 1
Local signalling	Green LED for power on Red LED for fault Reports when the preset threshold is reached
Type of setting	Measurement range by selected by wiring Overvoltage by switch Undervoltage by switch
Tripping threshold	10...100 %
Analogue input range	10...100 V AC 10...100 V DC 50...500 V AC 50...500 V DC
Hysteresis	5...50 %
Time delay range	0.1...10 s
Accuracy error	+/- 10 %
[Us] rated supply voltage	230 V AC 50/60 Hz
Power consumption	3 VA
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	4
Colour	White
Connections - terminals	Tunnel type terminals rigid

Environment

ambient air temperature for operation	-5...55 °C
---------------------------------------	------------

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1312 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.