



Figure similar

Model	
product designation	tap-off unit for BD2 busbar trunking system
operating voltage / at AC	
<ul style="list-style-type: none"> at 50 Hz / rated value / maximum 	500 V
<ul style="list-style-type: none"> at 60 Hz / rated value / maximum 	500 V
Protection class	
protection class IP	IP54
Main circuit	
operating frequency / rated value	
<ul style="list-style-type: none"> minimum 	50 Hz
<ul style="list-style-type: none"> maximum 	60 Hz
operating current	
<ul style="list-style-type: none"> for circuit 1 / at AC / at 50 Hz / rated value / maximum 	25 A
<ul style="list-style-type: none"> for circuit 1 / at AC / at 60 Hz / rated value / maximum 	25 A

Connections

- | | |
|--|----------------------|
| • connectable conductor cross-section / in the outgoing unit / minimum | 0.75 mm ² |
|--|----------------------|

Tap-off points

outgoing unit version	cable entry
design of short-circuit and overloading protection / in the outgoing unit	3-pole S27 fuse base
Size of the outgoing feeder	2
number of poles / of the outgoing feeder	5

Mechanical Design

height	160 mm
width	205 mm
length	320 mm
number of width units	8
product component / locking mechanism	Yes

Certificates

Declaration of Conformity



EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=BVP:203136>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/BVP:203136>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=BVP:203136

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>