

# Product data sheet

## 6280-1 CT

EAN-No. 4000896026005



Length: 181 mm · Torque range min-max: 2 – 10 Nm · Accuracy: 2 % · 



- Plug connection for holding insert tools
- **Accuracy  $\pm 2\%$  of the scale value** (in the direction of actuation)  
Can be used for right-hand and left-hand threads by turning the insert tool
- Safe:
  - Haptic (close-gap release)
  - Audible ("click" sound)
- With calibration certificate and serial number
- Especially slim design thanks to spring-loaded puller sleeve for locking the setting values
- Safe and fast adjustment of the desired torque value by turning the handle
- DIN EN ISO 6789-2:2017
- Made in Germany
- Output: 
- Dimensions: 181 mm
- Net weight: 0.32 kg
- For manual operation
- Torque range min-max: 2 – 10 Nm
- Accuracy: 2 %
- Scale Graduation (Nm): 0.2 Nm
- Effective torque wrench length min.-max. l1 mm: 160.40 – 154.40 Nm
- Actuating force min.-max. kg: 1.3 – 6.6 kg
- Inside micrometre of the adjusting tool l2: 19.5 mm
- Head Thickness a: 17 mm
- Head Width b: 22 mm
- **No more turning back:** Continuous long-term tests on the 5000 series and 6000 series of HAZET torque wrenches have demonstrated that turning them back to the smallest scale value is not required

SYSTEM 6200-1 CT insert torque wrench · 2 – 500 Nm · with insert square · accuracy  $\pm 2/4\%$