

40VMax Random Orbit Sander XGT®

BO001CG

125 mm

Model BO001CG is a battery powered random orbit sander powered by a 40Vmax XGT Li-Ion battery. Excellent maneuverability has been achieved by using a connector-style connection to the battery, reducing the load on hand and further keeping the overall height low.

The main features and benefits are: A connector connection to the battery, Net type abrasive discs, Pad saver discs, Compatible with AWS (Auto-start Wireless System).



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Orbits per Minute	6000 - 10000 min ⁻¹
AWS ready	✓
Sanding pad diameter	125 mm
Sanding Disc Diameter	125 mm
Sanding Orbit Diameter	5 mm
Sound Pressure Level (L _{pA})	78 dB(A)
Product net weight	0,92 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,7 - 2,9 kg
Product Dimensions (L x W x H):	234 x 123 x 96 mm
Vibration Level, Sanding Metal Plate	3,2 m/s ²
Vibration Uncertainty (K Factor), Sanding Metal Plate	1,5 m/s ²

User benefits

- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Electric brake for maximum productivity and increased operator safety
- Brushless maintenance-free and long-life motor

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing