




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Holder**

Primary Product Color: **Ivory**

Primary Product Material: **PA 66**

Number of Positions: **26**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Connector Hardware Accessory Type	Holder
Hardware Accessory Function	Mounting

Configuration Features

Number of Positions	26
---------------------	----

Body Features

Primary Product Color	Ivory
Primary Product Material	PA 66

Housing Features

Centerline (Pitch)	2 mm[.079 in]
--------------------	---------------

Dimensions

Product Width	8.5 mm[.334 in]
Row-to-Row Spacing	6.6 mm
Product Length	30.3 mm[1.193 in]
Product Height	8.3 mm[.326 in]
Wire Size	30 – 22 AWG



Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Packaging Features

Packaging Method	Bag
Packaging Quantity	750

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-AM7017-C7671
Common Termination Contacts —
POWER TRIPLE LOCK



TE Part # 1-179228-3
CT CRIMP-2 REC HSG 13P NATURAL



TE Part # CAT-3980700-DRWBSV
CT 2mm Dbl Row Assembly w/Boss:
Vert.




TE Part # 2-292138-6
CT DOUBLE ROW ASSY H 26P HDR N
Vert.


Also in the Series | AMP CT



Connector Contacts(8)



Connector Hardware(46)



PCB Headers & Receptacles(756)



Rectangular Connector Housings(72)



Rectangular Power Connectors(906)



Standard Rectangular Connectors(158)



Wire-to-Board Connector Assemblies
& Housings(97)



Wire-to-Board Headers & Receptacles
(756)

Customers Also Bought



TE Part #4-292249-2
1.5 MINI CT LATTICE PLUG/KIT K




TE Part #1-179472-8
CT DBL ROW HOLDER,CRIMP,18P,NA



TE Part #292215-7
MINI CT SGL RELAY 7P NAT



TE Part #917802-2
DYNAMIC D-5 TAB CONT. AU (S)



TE Part #177899-1
POWER DBL LOCK PLUG HSG 3P



TE Part #172142-2
EIS LOW PROFILE HSG 2P NATURAL



TE Part #3-917809-2
DYNAMIC D-5 TAB HSG D/R 4P X-Y



TE Part #1-2355088-7
MICRO CT CONN MT REC
ASSEMBLY 17P



Documents

Product Drawings

CT DBL ROW HOLDER,CRIMP,26P,NA

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-179472-6_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-179472-6_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-179472-6_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Crimping AMP 2.0mm Pitch CT Receptacle Contact

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English