

Product datasheet

Specifications



Ribbed door + lock syst. for Thalassa PHD enclosure - 127

Local distributor code:

403419337

NSYDPHD127R

 **Discontinued on:** 9 Feb 2023

EAN Code: 3606480841385

 **Discontinued**

Main

Range	Thalassa
Offer type	Spare part
Accessory / separate part category	Enclosure accessory
Product or component type	Door
Application	Heavy duty
For enclosure nominal dimensions	- H: 1393 mm W: 750 mm
Mounting location	Front
Range compatibility	Thalassa Thalassa PHD suitable enclosure
Device composition	hinges lock door door retainer handle
Quantity per set	Set of 1

Complementary

Material	Polyester double reinforced with fibreglass
Colour	Grey (RAL 7035)
Key number	1242 E
Door type	Anti-posting
Door opening side	Reversible (120 °)

Environment

IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Fire resistance conforming to EN 1794-2: 2011

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	77.500 cm
Package 1 Length	127.500 cm
Package 1 Weight	11.132 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

[Environmental Disclosure](#)[Product Environmental Profile](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	1341ad4e-77b9-40e3-bab0-32043fbc5959

Use Again

 Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No