

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,1996 .

© COPYRIGHT 1996


BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC


DIST

REVISIONS


| P | LTR | DESCRIPTION | ECN           | DATE       | DWN    | APVD |
|---|-----|-------------|---------------|------------|--------|------|
|   | C   | REVISED     | FJ00-1335-97  | 5/FEB '97  | K.I.H. |      |
|   | D   | REVISED     | FJD0-0025-03  | 21/FEB '03 | T.S    | S.M  |
|   | E   | REVISED     | FJD0-0120-03  | 7/MAY '03  | T.S    | S.M  |
|   | F   | REVISED     | FJD0-0039-03  | 2/JUN '03  | T.S    | S.M  |
|   | F1  | REVISED     | ECR-05-006870 | 15-JUL '05 | T.S    | P.M  |
|   | F2  | REVISED     | ECO-10-000445 | 09JAN10    | KK     | AEK  |



(1- -2,1- -3)  
(KEYING:X)



(2- -2,2- -3)  
(KEYING:Y)




AMP マーク  
AMP MARK

シリーズ マーク  
SERIES MARK

デートコード  
DATE CODE

回路番号  
CIRCUIT NO



リテンションレグ  
RETENTION LEG

コンタクト半田付部  
CONTACT TAIL

NOTES

1. MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC  
POLYESTER(94V-0), COLOR: BLACK  
TAB CONTACT: COPPER ALLOY  
RETENTION LEG: BRASS

2. FINISH (CONTACT AREA): 0.38μm MIN GOLD PLATING  
OVER Ni PLATING

3. FINISH (CONTACT AREA): 0.76μm MIN GOLD PLATING  
OVER Ni PLATING

4. FINISH (RETENTION LEG): TIN PLATED  
(CONTACT TAIL) OVER NICKEL

コネクタ外形  
OUTLINE OF HEADER HOUSING

ラウンド 2-φ3MIN  
ROUND DIA 3MIN 2PLACES

2-φ2  
DIA 2 2PLACES

6-φ1.8  
DIA 1.8 6PLACES

推奨基板取付け寸法 (公差: ±0.05)  
PC 基板厚: 1.6 ~ 2.4 ± 0.1  
(コネクタ搭載面)

PC 基板厚: 3.2 ± 0.1  
6-353082-2 ONLY

6-353082-2 ONLY

RECOMENDED PC BOARD HOLE PATTERN (TOL: ±0.05)  
PC BOARD THICKNESS: 1.6 ~ 2.4 ± 0.1  
(CONNECTOR MOUNT SIDE)

PC BOARD THICKNESS: 3.2 ± 0.1  
6-353082-2 ONLY

注 記

1. 材料: ハウジング: ガラス入り熱可塑性  
ポリエステル樹脂 (94V-0), 色: 黒  
タブ コンタクト: 銅合金  
リテンション レグ: 黄銅

2. めっき: コンタクト: 全面Ni下地  
接触部: 0.38μm MIN金めっき


3. めっき: コンタクト: 全面Ni下地  
接触部: 0.76μm MIN金めっき

4. めっき: リテンションレグとコンタクト半田付部  
: ニッケル下地のの上にスズめっき

|          |                    |                 |            |
|----------|--------------------|-----------------|------------|
| Y        | 4                  | 3               | 2-353082-3 |
|          | 4                  | 2               | 2-353082-2 |
| X        | 4                  | 3               | 1-353082-3 |
|          | 4                  | 2               | 6-353082-2 |
|          | 4                  | 2               | 1-353082-2 |
| KEY TYPE | コンタクトのめっき (FINISH) | 製品番号 (PART NO.) |            |

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.  
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING  
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:  
単位 単位: mm



MATERIAL

注記参照

SEE NOTE

TOLERANCES UNLESS  
OTHERWISE SPECIFIED

一般公差  
10% : ±0.3  
30% : >10 : ±0.35  
10% : >30 : ±0.4  
ANGLE : ±3°

FINISH

注記参照

SEE NOTE

DWN K.IKEDA 4/JUL/'96  
CHK Y.Ishikawa 4/JUL/'96  
APVD S.Manabe 4/JUL/'96

PRODUCT SPEC

108-5453

APPLICATION SPEC

114-5206

WEIGHT

CUSTOMER DRAWING

WIRE RANGE

総合電線断面積

INSULATION DIA

被覆外径

tyco  
Electronics

Tyco Electronics AMP K.K.  
Kawasaki, Japan

NAME 名称 1列 ヘッダーアセンブリ 3P  
(垂直 タイプ)  
SINGLE ROW HEADER ASS'Y 3P("V" TYPE)  
<DYNAMIC D-5200 S>

SIZE A3 CAGE CODE 00779 DRAWING NO 番号 C-353082

SCALE 尺 1-1 SHEET 1 OF 2 REV F2

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,1996 .

© COPYRIGHT 1996

BY AMP INCORPORATED. ALL RIGHTS RESERVED.


LOC

DIST


REVISIONS

変更

| P | LTR | DESCRIPTION | ECN | DATE | DWN | APVD |
|---|-----|-------------|-----|------|-----|------|
|   |     | SEE 1 OF 2  |     |      |     |      |
|   |     |             |     |      |     |      |
|   |     |             |     |      |     |      |
|   |     |             |     |      |     |      |




8,9-353082-2;AS SHOWN  
SEQUENTIAL TYPE



(9-353082-2)  
(KEYING:Y)


GROUND POST ②

SIGNAL POST ①




SECT "A"- "A"

(SCALE:2-1)



|     | 回路番号     |          |          |
|-----|----------|----------|----------|
|     | 1        | 2        | 3        |
| 1 列 | ① Signal | ① Signal | ② Ground |

POINT OF SEQUENTIAL



リテンションレグ  
CONTACT TAIL

NOTES

1. MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC  
POLYESTER(94V-0),COLOR:BLACK  
TAB CONTACT:COPPER ALLOY  
RETENTION LEG:BRASS

②. FINISH(CONTACT AREA):0.38μMIN GOLD PLATING  
OVER Ni PLATING

③. FINISH(CONTACT AREA):0.76μMIN GOLD PLATING  
OVER Ni PLATING

④. FINISH(RETENTION LEG): TIN PLATED  
(CONTACT TAIL) OVER NICKEL

注記

1. 材料:ハウジング:ガラス入り熱可塑性

ポリエステル樹脂 (94V-0),色:黒

タブ コンタクト:銅合金

リテンション レグ:黄銅

②. めっき:コンタクト:全面Ni下地

接触部:0.38μMIN金めっき

③. めっき:コンタクト:全面Ni下地

接触部:0.76μMIN金めっき

④. めっき:リテンションレグとコンタクト半田付部


:ニッケル下地の上にスズめっき

⑤. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING  
PER D.RENAUD/D.SINISI

|          |                       |                    |  |
|----------|-----------------------|--------------------|--|
| Y        |                       |                    |  |
| X        |                       |                    |  |
| KEY TYPE | コンタクトのめっき<br>(FINISH) | 製品番号<br>(PART NO.) |  |

OBSOLETE ⑤

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:  
単位 ㎜TOLERANCES UNLESS  
OTHERWISE SPECIFIED

一般公差  
10% : ±0.3  
30% : ±0.35  
10% : ±0.4  
ANGLE : ±3°

MATERIAL

注記参照

SEE NOTE

FINISH

注記参照

SEE NOTE

DWN K.IKEDA 4/JUL/'96

CHK Y.Ishikawa 4/JUL/'96

APVD S.Manabe 4/JUL/'96

PRODUCT SPEC

108-5453

APPLICATION SPEC

114-5206

WEIGHT

CUSTOMER DRAWING

WIRE RANGE

適合電線断面積

INSULATION DIA

被覆外径

tyco  
ElectronicsTyco Electronics AMP K.K.  
Kawasaki, Japan

1列 ヘッダーアセンブリー 3P  
(垂直 タイプ)  
SINGLE ROW HEADER ASS'Y 3P("V"TYPE)  
<DYNAMIC D-5200 S>

SIZE A3 CAGE CODE 00779 DRAWING NO  
⑤-353082

SCALE 1-1 SHEET 2 OF 2 REV F2