



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance



Primary Product Color: **Black**

Connector & Contact Retention Accessory Type: **Retainer**

Primary Product Material: **PBT GF**

Operating Temperature Range: **-40 – 120 °C [-40 – 248 °F]**

Features

Product Type Features

Connector & Contact Retention Accessory Type	Retainer
--	----------

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Other

Serviceable	No
-------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2112649-1  
RETAINER, TE, 2X3 POS




TE Part # 2112651-1  
6POS, MQS, REC HSG, ASSY


Customers Also Bought




TE Part #4-929080-5  
2POS MQS REC COD D



TE Part #2141868-3  
TAB 1.2X0.6, SWS; 0,08-0,15SQMM



TE Part #2208829-1  
RETAINER, FOR MCON1.2 CB



TE Part #1-2344408-1  
9POS, CHARGE INLET ASSY, CHADEMO





TE Part #2-2141894-1  
JPT A REC 2.8 Contact SWS Au



TE Part #2331462-1  
DIA 8MM,PIN TERMINAL,WELDING  
90 DEG



TE Part #2292534-1  
PROTECTION CAP,TE,WATER DRAIN  
90 DEG



TE Part #2331463-1  
DIA 8MM,PIN TERMINAL,WELDING  
90 DEG

TE Part #1-2330295-7  
DIA 3MM,TERMINAL,CHARGING  
TERMINAL



TE Part #1563625-2  
HPF 1.5 REC SWS AU

Documents

Product Drawings

RETAINER,TE,2X3 POS,ASSY

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2112650-1\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2112650-1\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2112650-1\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Product Specification

German