

MACX-MR-V-600-PT - Monitoring relay



1336507

<https://www.phoenixcontact.com/in/products/1336507>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



1-phase voltage monitoring relay, 24 V AC/DC ... 240 V AC/DC wide range power supply, with adjustable threshold values, response delay, and the functions can be selected by configuration.

Commercial data

Item number	1336507
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CK4
Product key	DK6611
GTIN	4063151636562
Weight per piece (including packing)	198.4 g
Weight per piece (excluding packing)	195 g
Customs tariff number	85364900
Country of origin	CN

MACX-MR-V-600-PT - Monitoring relay



1336507

<https://www.phoenixcontact.com/in/products/1336507>

Technical data

Product properties

Product type	Voltage monitoring relay
Operating mode	Closed circuit or wire break

Insulation characteristics: Railway standard

Overvoltage category	III
Pollution degree	3

Electrical properties

Rated impulse withstand voltage	6 kV
Service life electrical	approx. 1×10^5 cycles, resistive load 2000 V A
Maximum power dissipation for nominal condition	15 W
Mains type	1-phase

Railway standard

Rated insulation voltage	600 V
--------------------------	-------

Electrical isolation

Electrical isolation	300 V
----------------------	-------

Supply

Supply voltage range	24 V AC ... 240 V AC -15 % ... +10 %
	24 V DC ... 240 V DC -25 % ... +30 %
Nominal power consumption	15 VA (1.5 W)

Input data

Input name	Measuring input
Measured value	DC, AC sine (40 Hz ... 500 Hz)
Input voltage range	0 V AC/DC ... 600 V AC/DC
Frequency range	48 Hz ... 400 Hz
Maximum temperature coefficient	0.05 %/K
Setting range for response delay	0 s ... 99.9 s
Function	Undervoltage
	Overvoltage
	Window
Basic accuracy	1 % (>50V, $\pm 0.5V$ (0...50V))
Repeat accuracy	0.5 %
Recovery time	200 ms

Output data

Switching

Contact switching type	2 floating changeover contacts
Maximum switching voltage	250 V AC

MACX-MR-V-600-PT - Monitoring relay



1336507

<https://www.phoenixcontact.com/in/products/1336507>

Interrupting rating (ohmic load) max.	2000 VA (8 A/250 V AC)
Output fuse	8 A (fast-blow)

Connection data

Connection method	Push-in connection
Stripping length	10 mm
Conductor cross section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 14
Tightening torque	0.5 Nm ... 0.6 Nm (5 lb in ... 7 lb in)

Dimensions

Width	22.5 mm
Height	109 mm
Depth	114 mm

Material specifications

Flammability rating according to UL 94	V0
Housing insulation material	PBT

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP40 (Housing)
	IP20 (Connection terminal blocks)
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 %

Approvals

CE

Identification	CE-compliant
----------------	--------------

UL, USA/Canada

Identification	UL/C-UL Listed UL 508
----------------	-----------------------

CCC

Identification	GB/T 14048.5
----------------	--------------

Electronic devices in rail vehicles

Operating temperature class	OT4
Class of extended operating temperature upon activation	ST2
Temperature change class	H1
Interruption of the power supply/supply changeover	S2
	S3/C1
	C2

MACX-MR-V-600-PT - Monitoring relay



1336507

<https://www.phoenixcontact.com/in/products/1336507>

Hazard levels	HL1
	HL2
	HL3
Protective coating	PC2
Shock (operation)	Category 1
Vibration (operation)	Class B

EMC data

Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive
Noise immunity	EN 61000-6-2
Noise emission	EN 61000-6-4

Standards and regulations

Railway standard

Standard designation	EN 50155, GB/T 25119
----------------------	----------------------

Mounting

Assembly note	on standard DIN rail NS 35 in accordance with EN 60715
Mounting position	any

MACX-MR-V-600-PT - Monitoring relay


1336507

<https://www.phoenixcontact.com/in/products/1336507>



Drawings

Schematic diagram




MACX-MR-V-600-PT - Monitoring relay

1336507

<https://www.phoenixcontact.com/in/products/1336507>



Block diagram



MACX-MR-V-600-PT - Monitoring relay



1336507

<https://www.phoenixcontact.com/in/products/1336507>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1336507>



CCC

Approval ID: 2024010303656845



cULus Listed

Approval ID: E172140

MACX-MR-V-600-PT - Monitoring relay



1336507

<https://www.phoenixcontact.com/in/products/1336507>

Classifications

ECLASS

ECLASS-11.0	27371801
ECLASS-13.0	27371801
ECLASS-12.0	27371801

ETIM

ETIM 9.0	EC001438
----------	----------

MACX-MR-V-600-PT - Monitoring relay



1336507

<https://www.phoenixcontact.com/in/products/1336507>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5ea2dded-49e6-47e5-8a62-f8b50cff72ec

MACX-MR-V-600-PT - Monitoring relay

1336507

<https://www.phoenixcontact.com/in/products/1336507>



Accessories

MACX-BLUETOOTH-NFC - Adapter

1142259

<https://www.phoenixcontact.com/in/products/1142259>



Bluetooth NFC adapter

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in